



Product: [FS3L216NG](#)

Outdoor Loose Tube OM3 216 Fibers

Product Description

FX Outdoor Loose-Tube (Single Jacket) OM3 216 Fibers OFN

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Campus Area Network, Long Haul, Backbone |
|------------------------|--|

Fiber Specifications

| | |
|----------------------|-----------|
| Fiber Type: | OM3 |
| Fiber Core Diameter: | 50/125 µm |
| Fiber Diameter: | 250 µm |
| Fiber Count: | 216 |
| Fiber Color Coding: | TIA-598-D |

Cable Construction

| | |
|----------------------------|--------------------|
| Number of Active Subunits: | 18 |
| Fibers Per Subunit: | 12 |
| Subunit Waterblocking: | Gel Filled |
| Subunit Diameter: | 0.098 in (2.5 mm) |
| Central Strength Member: | Upjacketed GRP |
| Core Wrap: | Waterblocking Tape |
| Cable Core Waterblocking: | Waterblock Tape |

Inner Jacket Specifications

| | |
|-----------|-------------------|
| Material: | PE - Polyethylene |
|-----------|-------------------|

Outer Jacket Specifications

| | |
|---------------------|----------------------------|
| Strength Member: | Waterblocking Aramid Yarns |
| Jacket Material: | PE - Polyethylene |
| Nom. Diameter: | 0.892 in (22.7 mm) |
| Color: | Black |
| Number of Ripcords: | 1 |

Optical Characteristics

| Wavelength | 850 nm | 1300 nm |
|--|-------------|------------|
| Max. Attenuation | 3.0 dB/km | 1.0 dB/km |
| 1 Gigabit Ethernet Performance | 1000 | 550 |
| 10 Gigabit Ethernet Performance | 300 m | -- |
| Min. Effective Modal Bandwidth (EMB) | 2000 MHz-km | -- |
| Min. Overfilled Launch (OFL) Bandwidth | 1500 MHz-km | 500 MHz-km |

Mechanical Characteristics

| | |
|---------------------------------------|--------------|
| Min. Bend Radius During Installation: | 15x Cable OD |
|---------------------------------------|--------------|

| | |
|--|-------------------------|
| Min. Bend Radius During Operation: | 10x Cable OD |
| Max. Tensile Strength During Installation: | 2670 N (600 lbf) |
| Max. Tensile Strength During Operation: | 800 N (180 lbf) |
| Crush Resistance: | 220 N/cm |
| Bulk Cable Weight: | 125 lbs/kft (186 kg/km) |

Temperature Range

| | |
|---------------------------------|--------------|
| Installation Temperature Range: | -30C to +70C |
| Operating Temperature Range: | -40C to +70C |
| Storage Temperature Range: | -40C to +75C |

Standards and Compliance

| | |
|----------------------------|--------------------|
| Environmental Suitability: | Outdoor, Burial |
| Sustainability: | CA Prop 65 |
| ICEA Compliance: | S-87-640 |
| TIA/EIA Compliance: | ANSI/ICEA S-87-640 |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.84 Revision Date: 11-09-2022 |
|----------------------|---|

Part Numbers

Variants

| Item # | Color | Putup Type | UPC |
|-----------|-------|------------|--------------|
| FS3L216NG | Black | Reel | 612825376637 |

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.