



Product: [FS1L0366F](#)

Loose Tube OM1 36F OSP Armor Unitized(6F) Gel

Product Description

FX Outdoor Loose Tube OM1 36 Fibers OSP Corrugated Steel Tape Armor Sub-Units(6F) Gel Black Jacket

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Campus Area Network, Long Haul, Backbone |
|------------------------|--|

Fiber Specifications

| | |
|----------------------|------------------|
| Fiber Type: | OM1 |
| Fiber Core Diameter: | 62.5/125 μ m |
| Fiber Diameter: | 250 μ m |
| Fiber Count: | 36 |
| Fiber Color Coding: | TIA-598-D |

Cable Construction

| | |
|----------------------------|-------------------|
| Number of Active Subunits: | 6 |
| Fibers Per Subunit: | 6 |
| Subunit Waterblocking: | Gel Filled |
| Subunit Diameter: | 0.078 in (2.0 mm) |
| Central Strength Member: | Upjacketed GRP |
| Core Wrap: | Nomex tape |
| Cable Core Waterblocking: | Waterblock Tape |

Inner Jacket Specifications

| | |
|---------------------|--------------------------|
| Strength Member: | Aramid Yarns |
| Material: | PVC - Polyvinyl Chloride |
| Nom. Diameter: | 0.324 in (8.2 mm) |
| Color: | Black |
| Number of Ripcords: | 2 |

Armor Specifications

| | |
|--------------------------|-----------------------------|
| Armor Type and Material: | CST - Corrugated Steel Tape |
|--------------------------|-----------------------------|

Outer Jacket Specifications

| | |
|---------------------|--------------------------|
| Jacket Material: | PVC - Polyvinyl Chloride |
| Nom. Diameter: | 0.530 in (13.5 mm) |
| Color: | Black |
| Number of Ripcords: | 2 |

Optical Characteristics

| Wavelength | 850 nm | 1300 nm |
|--------------------------------|------------|-----------|
| Max. Attenuation | 3.25 dB/km | 1.0 dB/km |
| 1 Gigabit Ethernet Performance | 300 m | 550 m |

| | | |
|--|------------|------------|
| 10 Gigabit Ethernet Performance | 33 m | - |
| Min. Restricted Mode Launch | 220 MHz.km | - |
| Min. Overfilled Launch (OFL) Bandwidth | 200 MHz.km | 500 MHz.km |

Mechanical Characteristics

| | |
|--|------------------|
| Min. Bend Radius During Installation: | 20x Cable OD |
| Min. Bend Radius During Operation: | 10x Cable OD |
| Max. Tensile Strength During Installation: | 2670 N (600 lbf) |
| Max. Tensile Strength During Operation: | 800 N (180 lbf) |
| Crush Resistance: | 440 N/cm |
| Bulk Cable Weight: | 102 |

Temperature Range

| | |
|---------------------------------|----------------|
| Installation Temperature Range: | -30°C to +60°C |
| Operating Temperature Range: | -40°C to +70°C |
| Storage Temperature Range: | -40°C to +70°C |

Standards and Compliance

| | |
|----------------------------|--------------------|
| Environmental Suitability: | Outdoor |
| Sustainability: | CA Prop 65 |
| ICEA Compliance: | S-87-640 |
| TIA/EIA Compliance: | ANSI/ICEA S-87-640 |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.86 Revision Date: 11-09-2022 |
|----------------------|---|

Part Numbers

Variants

| Item # | Color | Putup Type | UPC |
|-----------|-------|------------|--------------|
| FS1L0366F | Black | Reel | 612825388418 |

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.