



**Product:** [FX Adapter Strip LC Duplex](#)



FX Adapter Strip LC Duplex

## Product Description

FiberExpress Adapter Strip, loaded 12 LC Duplex Singlemode Adapters Black

## Technical Specifications

### Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room

### Construction

Weight:	0.093 kg
Height:	1 m
Width:	6.5
Length:	1.15 ft

### Physical Specifications

Max Capacity:	24 Fibers, 12 LC Duplex Singlemode Adapter
---------------	--

### Mechanical Characteristics

Front Connection:	Flush
Termination Style:	Front
Termination Type:	Front and Rear
Type of Connection:	Mated Connection
Cable/Connector Retention:	11.250 lbs.
Connector/Hardware Retention:	11.25 lbs
Durabilities@Termination1:	500 cycles

### Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +75°C

### Product Material

#### Materials

Element	Description	Color
Steel	Connector Body	Metal
LC	Connectory Body Type	
Zirconia-Ceramic	Adapter Sleeve	

### Related Part Numbers

Included Parts:	Dust Caps
-----------------	-----------

#### Variants

Item #	Color	Port Count	Adapter Color
--------	-------	------------	---------------

AX101729	Black	6 Port	Beige
AX101731	Black	6 Port	Blue

## Product Notes

Packaging:	Individually packaged in a plastic bag. Standard pack of 30 units.
Notes:	For additional information about this product, visit our web site at <a href="http://www.belden.com">http://www.belden.com</a> .

## History

Update and Revision:	Revision Number: 0.55 Revision Date: 11-09-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.