



**Product:** [GBWUF32](#)

Outdoor OFC MLT: ARAMID + PE + SWA + PE with 12 gel-free tubes of Ø1.9mm 132f SM OS2 G.657.A2.

## Product Description

Outdoor dry core optical fiber Multi Loose Tube cable with aramid yarns as strength member, polyethylene inner jacket, Steel Wire Armouring (Full Rodent Protected) armor and polyethylene outer jacket. Product feature: This cable has improved rodent protection by Steel Wire Armouring (Full Rodent Protected). Existing out of 12 gel-free tubes with a diameter of 1.9mm with 132 fibers (11t x 12f) SM OS2 G.657.A2.

## Technical Specifications

### Product Overview

|                        |                                                                                                                                                                                                                                                                                                                                 |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Construction Type:     | Multi Loose Tube                                                                                                                                                                                                                                                                                                                |
| Environmental Space:   | Outdoor                                                                                                                                                                                                                                                                                                                         |
| Suitable Applications: | For outdoor use in structured (data) wiring systems such as industrial backbone, campus backbone, building backbone (riser) and/or horizontal cabling. For outdoor use in networks for industrial, telecom, cable TV and/or broadcast. Easy to install in ducts, tunnels and trenches and/or tubes. Suitable for Direct Burial. |

### Construction

#### Fiber Cable Construction

| Fiber Type                    | Fiber Grade acc. ITU-T                                                                                  | Fiber Count | Subunit Color                                                                                     |
|-------------------------------|---------------------------------------------------------------------------------------------------------|-------------|---------------------------------------------------------------------------------------------------|
| OS2                           | G.657A2                                                                                                 | 132         | TIA coding (Gxxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink |
| Fiber Color Code:             | TIA coding (Gxxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua |             |                                                                                                   |
| Central Strength Member Type: | GRP                                                                                                     |             |                                                                                                   |
| Cable Core Water Tight:       | Yes                                                                                                     |             |                                                                                                   |
| Cable Core Water Blocking:    | Waterblocking Aramid Yarns + Tape                                                                       |             |                                                                                                   |
| Bulk Cable Weight:            | 462 kg/km                                                                                               |             |                                                                                                   |

### SubUnit Specifications

|                              |          |
|------------------------------|----------|
| Number of Active Subunits:   | 11       |
| Number of Subunit Positions: | 12       |
| Fibers Per Subunit:          | 12       |
| Subunit Diameter:            | 1.9 mm   |
| Subunit Waterblocking:       | Gel Free |

### Jacket Specifications

|                    |               |
|--------------------|---------------|
| Number of Jackets: | Double Jacket |
| Type of Armor:     | Steel Wire    |

### Inner Jacket

|           |                   |
|-----------|-------------------|
| Material: | PE - Polyethylene |
|-----------|-------------------|

### Outer Jacket Specifications

#### Outer Jacket

| Material          | Color | Nominal Diameter | Ripcord |
|-------------------|-------|------------------|---------|
| PE - Polyethylene | Black | 18.1 mm          | Yes     |

Optical Characteristics

|                                 |            |
|---------------------------------|------------|
| Maximum Attenuation at 1310 nm: | 0.40 dB/km |
| Maximum Attenuation at 1550 nm: | 0.30 dB/km |
| Maximum Attenuation at 1625 nm: | 0.30 dB/km |

Mechanical Characteristics

Mechanical Tests

| Description                                           | Tested Standard    | Requirement/Value             | According to Family Specification |
|-------------------------------------------------------|--------------------|-------------------------------|-----------------------------------|
| Cable Min. Bend Radius Installation (Short Term)      | IEC 60794-1-21-E6  | 362 mm                        | IEC 60794-3-10                    |
| Cable Min. Bend Radius Operation (Long Term)          | IEC 60794-1-21-E11 | 362 mm                        | IEC 60794-3-10                    |
| Cable Max. Tensile Strength Installation (Short Term) | IEC 60794-1-21-E1  | 2850 N (641 lbf)              | IEC 60794-3-10                    |
| Cable Max. Tensile Strength Operation (Long Term)     | IEC 60794-1-21-E1  | 950 N (214 lbf)               | IEC 60794-3-10                    |
| Cable Max. Crush Resistance Installation (Short Term) | IEC 60794-1-21-E3  | 22 kN/m                       | IEC 60794-3-10                    |
| Cable Max. Crush Resistance Operation (Long Term)     | IEC 60794-1-21-E3  | 11 kN/m                       | IEC 60794-3-10                    |
| Cable Impact Resistance                               | IEC 60794-1-21-E4  | 10 J, 300 mm Radius, 3 Cycles | IEC 60794-3-10                    |
| Cable Torsion Resistance                              | IEC 60794-1-21-E7  | 180°, 2 m, 10 cycles          | IEC 60794-3-10                    |

Temperature Range

|                                 |                  |
|---------------------------------|------------------|
| Operating Temperature Range:    | -30 °C to +70 °C |
| Installation Temperature Range: | -5 °C to +50 °C  |
| Storage Temperature Range:      | -30 °C to +70 °C |

Standards

|                                   |                            |
|-----------------------------------|----------------------------|
| UL Rating/Flame Test:             | Non-UL Rated               |
| REACH:                            | Compliant                  |
| ISO/IEC Compliance:               | IEC 60794, ISO/IEC 11801-1 |
| EU Directive 2011/65/EU (RoHS 2): | Compliant                  |
| UV/ Sunlight Protection:          | Yes                        |

History

|                      |                                                |
|----------------------|------------------------------------------------|
| Update and Revision: | Revision Number: 0.4 Revision Date: 09-23-2025 |
|----------------------|------------------------------------------------|

© 2025 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.