



**Product:** [FX-EASE PP 1U 24F SM SC/APC](#)

1U FX@EASE 24-port half loaded (12) Duplex SC/APC Patch Panel - without pigtailloaded

**Product Description**

1U FiberExpress@EASE 24-port half loaded (12) Duplex SC/APC Termination/Splice Patch Panel - without pigtaills

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
Suitable Applications:	FiberExpress@ease Solutions, Backbone, Telecommunications Room, Main Distribution Room, Workstation Area

**Construction**

Weight:	2.500 kg
Height:	44 mm
Width:	482 mm
Depth:	251.5 mm

**Physical Specifications**

Max Capacity:	48
---------------	----

**Mechanical Characteristics**

Front Connection:	Flush
Footprint/Type:	SC

**Temperature Range**

Operating Temp Range:	-10°C To +60°C
Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-10°C To +60°C

**Product Material**

**Materials**

Description	Material	Color
Panel	Textured powder coated Steel	Black
Fiber Adapter	Plastic, Half loaded with 12 SC duplex adapters	Green
Accessories inside panel	2 pcs splice trays/holders, cable management, 2 pcs Cable glands, angled cable entry brackets	

**Standards**

TIA/EIA Compliance:	ISO/IEC 11801-1:2017
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

**Part Number**

Related Parts:	To Fully load the panel, 1 piece NN-5.SM12. and 1 piece NN-SPL.TR have to be ordered.
----------------	---

**Variants**

Item #	Color	EAN
NN01405.AM12	Black	8719605177353

## Product Notes

Packaging:	Individually packaged in a box.
------------	---------------------------------

## History

Update and Revision:	Revision Number: 0.27 Revision Date: 12-15-2021
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.