



Product: [GMMKD12](#)

Outdoor Tactical bare fiber mini distribution cable PUR jacket 12f MM OM3.

Product Description

Outdoor Tactical bare fiber mini optical fiber distribution cable with Polyurethane (PUR) outer jacket. 12 fibers MM OM3.

Technical Specifications

Product Overview

|                        |  |
|------------------------|--|
| Construction Type:     | Tactical   |
| Environmental Space:   | Indoor/Outdoor   |
| Suitable Applications: | The individual multi fibre units (of which this metal-free cable is composed) permits direct termination with MPO connectors. Extremely strong, rugged, survivable cable for severe environments. This cable is halogen-free, watertight and therefore suitable for indoor and outdoor use. The cable combines the ruggedness of tactical cable with the ultra-high density of micro-cable technology. Designed for rapid deployment in optical networks, high mechanical performance, and suitable for extreme environmental exposure. High fiber density allows for longer deployment lengths. Longer assembly lengths reduce the number of optical connections and enhance network performance. |

Construction

Fiber Cable Construction

| Fiber Type                | Fiber Count   | Subunit Color                |
|---------------------------|---|------------------------------|
| OM3                       | 12  | TIA coding (Gxxxxxx.T): Blue |
| Fiber Color Coding:       | TIA coding (Gxxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua |                              |
| Central Strength Member:  | GRP   |                              |
| Cable Core Water Tight:   | No  |                              |
| Cable Core Waterblocking: | Waterblocking Aramid Yarns  |                              |
| Bulk Cable Weight:        | 57 kg/km  |                              |

SubUnit Specifications

|                              |                            |
|------------------------------|----------------------------|
| Number of Active Subunits:   | 1                          |
| Number of Subunit Positions: | 4                          |
| Fibers Per Subunit:          | 12                         |
| Subunit Diameter:            | 2.1 mm                     |
| Subunit Waterblocking:       | Waterblocking Aramid Yarns |

Jacket Specifications

|                    |               |
|--------------------|---------------|
| Number of Jackets: | Single Jacket |
| Type of Armor:     | Non-Armored   |

Outer Jacket Specifications

Outer Jacket

| Material           | Color | Nominal Diameter | Ripcord |
|--------------------|-------|------------------|---------|
| PUR - Polyurethane | Black | 8.0 mm           | Yes     |

Optical Characteristics

|                              |           |
|------------------------------|-----------|
| Max. Attenuation at 1300 nm: | 1.0 dB/km |
| Max. Attenuation at 850 nm:  | 2.9 dB/km |

Mechanical Characteristics

Mechanical Tests

| Description   | Tested Standard    | Requirement/Value | According to Family Specification |
|---|--------------------|-------------------|-----------------------------------|
| Cable Min. Bend Radius Installation (Short Term)      | IEC 60794-1-21-E6  | 120 mm            | IEC 60794-2-20                    |
| Cable Min. Bend Radius Operation (Long Term)          | IEC 60794-1-21-E11 | 80 mm             | IEC 60794-2-20                    |
| Cable Max. Tensile Strength Installation (Short Term) | IEC 60794-1-21-E1  | 2000 N (450 lbf)  | IEC 60794-2-20                    |
| Cable Max. Crush Resistance Installation (Short Term) | IEC 60794-1-21-E3  | 50 kN/m           | IEC 60794-2-20                    |

Temperature Range

|                                 |                  |
|---------------------------------|------------------|
| Operating Temperature Range:    | -50 °C to +80 °C |
| Installation Temperature Range: | -20 °C to +65 °C |
| Storage Temperature Range:      | -50 °C to +80 °C |

Standards

|                                   |                            |
|-----------------------------------|----------------------------|
| UL Rating/Flame Test:             | Non-UL Rated               |
| IEC Flammability:                 | IEC 60332-1-2              |
| REACH:                            | Compliant                  |
| ISO/IEC Compliance:               | IEC 60794, ISO/IEC 11801-1 |
| EU Directive 2011/65/EU (RoHS 2): | Compliant                  |
| UV/ Sunlight Protection:          | Yes                        |

History

|                      |   |
|----------------------|---|
| Update and Revision: | Revision Number: 0.34 Revision Date: 09-17-2024 |
|----------------------|---|

© 2025 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.