



**Product:** [GMPZ0F0](#)



Outdoor Tactical empty tube patchcord PUR jacket 3.0mm furcation tube No fiber.

## Product Description

Outdoor Tactical empty tube patchcord with Polyurethane (PUR) outer jacket. 3.0mm furcation tube No fiber.

## Technical Specifications

### Product Overview

Construction Type:	Tactical
Environmental Space:	Indoor (Not Riser or Plenum)
Suitable Applications:	Breakout kits. Short distance applications for indoor use.

### Construction

#### Fiber Cable Construction

<b>Fiber Count</b>	
	0
Cable Core Water Tight:	Yes
Bulk Cable Weight:	5.8 kg/km

### Jacket Specifications

Number of Jackets:	Single Jacket
Type of Armor:	Non-Armored

### Outer Jacket Specifications

#### Outer Jacket

Material	Nominal Diameter	Ripcord
PUR - Polyurethane	3.0 mm	No

### Mechanical Characteristics

#### Mechanical Tests

Description	Tested Standard	Requirement/Value
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	60 mm
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	75 N (17 lbf)
Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	

### Temperature Range

Operating Temperature Range:	-30 °C to +70 °C
Installation Temperature Range:	-5 °C to +50 °C
Storage Temperature Range:	-30 °C to +70 °C

### Standards

UL Rating/Flame Test:	Non-UL Rated
REACH:	Compliant

ISO/IEC Compliance:	IEC 60794, ISO/IEC 11801-1
EU Directive 2011/65/EU (RoHS 2):	Compliant
UV/ Sunlight Protection:	Yes

### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	EAN
GMPZ0F0.002100	Orange	Reel	2,100 m	8719605076403

### History

Update and Revision:	Revision Number: 0.95 Revision Date: 09-17-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.