



**Product:** [GMRTE02](#) 

Outdoor Tactical tight buffered OFC: GLASS YARNS (impr. rodent protection)  
PUR jacket 2f MM OM4.

## Product Description

Outdoor Tactical tight buffered optical fiber cable with glass yarns as strength member and improved rodent protection with Polyurethane (PUR) outer jacket. 2 fibers MM OM4.

## Technical Specifications

### Product Overview

Construction Type:	Tactical
Environmental Space:	Indoor/Outdoor
Suitable Applications:	For outdoor and indoor use. These metal-free tactical cables have been designed for de-spooling and re-spooling repeatedly. Support all computer network applications such as FDDI, Gigabit Ethernet and ATM Easy to install. Not Recommended for direct burial. Core bonded Polyurethane inner and outer jacket providing simple installation. Glass-rovings between inner and outer jacket for improved mechanical strength.

### Construction

#### Fiber Cable Construction

Fiber Type	Fiber Count
OM4	2

Fiber Color Coding: TIA coding (Gxxxxx.T): Blue, Orange

#### Buffer Specification

Fiber Type	Buffer Construction	Buffer Material	Buffer Diameter
OM4	Tight	Nylon	0.9 mm

Cable Core Water Tight:

Yes

Cable Core Waterblocking:

Waterblocking Aramid Yarns + Glass Yarns

Bulk Cable Weight:

87 kg/km

### Jacket Specifications

Number of Jackets:	Double Jacket
Type of Armor:	Non-Armored

### Inner Jacket

Material:	PUR - Polyurethane
-----------	--------------------

### Outer Jacket Specifications

#### Outer Jacket

Material	Color	Nominal Diameter	Ripcord
PUR - Polyurethane	Black	9.2 mm	No

### Optical Characteristics

Max. Attenuation at 1300 nm:	0.9 dB/km
Max. Attenuation at 850 nm:	2.9 dB/km

## Mechanical Characteristics

### Mechanical Tests

Description	Tested Standard	Requirement/Value	According to Family Specification
Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E6	73.6 mm	
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	36.8 mm	
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	2400 N (540 lbf)	IEC 60794-2-20
Cable Max. Tensile Strength Operation (Long Term)		800 N (180 lbf)	
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3	5 kN/m	IEC 60794-2-20
Cable Max. Crush Resistance Operation (Long Term)	IEC 60794-1-21-E3	3 kN/m	IEC 60794-2-20

### Temperature Range

Operating Temperature Range:	-70 °C to +85 °C
Installation Temperature Range:	-5 °C to +50 °C
Storage Temperature Range:	-70 °C to +85 °C

### Standards

UL Rating/Flame Test:	Non-UL Rated
REACH:	Compliant
ISO/IEC Compliance:	IEC 60794, ISO/IEC 11801-1
EU Directive 2011/65/EU (RoHS 2):	Compliant
UV/ Sunlight Protection:	Yes

### History

Update and Revision:	Revision Number: 0.51 Revision Date: 09-17-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.