



Product: [GIPTDE1](#)

Indoor tight buffered patchcord LSZH jacket 2.8mm simplex MM OM3. CPR Eca.

Product Description

Indoor tight buffered patchcord with Low Smoke Zero Halogen outer jacket. 2.8mm simplex MM OM3. CPR Euroclass Eca.

Technical Specifications

Product Overview

Construction Type:	Interconnect
Environmental Space:	Indoor - Euroclass Eca
Suitable Applications:	Flexible terminating leads such as pigtails, patchcords and test leads. Support all computer network applications such as FDDI, Gigabit Ethernet and ATM. Short distance applications for indoor use.

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OM3	1

Fiber Color Coding:	TIA coding (Gxxxxx.T): Blue
---------------------	-----------------------------

Buffer Specification

Fiber Type	Buffer Construction	Buffer Material	Buffer Diameter
OM3	Tight	LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.9 mm

Cable Core Water Tight:	Yes
-------------------------	-----

Bulk Cable Weight:	7.2 kg/km
--------------------	-----------

SubUnit Specifications

Fibers Per Subunit:	1
---------------------	---

Jacket Specifications

Number of Jackets:	Single Jacket
--------------------	---------------

Type of Armor:	Non-Armored
----------------	-------------

Outer Jacket Specifications

Outer Jacket

Material	Nominal Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	2.8 mm	No

Table Notes:	Standard color: Orange. Available colors: Orange, Yellow, Turquoise, Erika Violet, Red, Blue, Green, Brown, Violet, Pink, Grey, White, Black, Lime Green
--------------	--

Optical Characteristics

Max. Attenuation at 1300 nm:	0.9 dB/km
------------------------------	-----------

Max. Attenuation at 850 nm:	2.9 dB/km
-----------------------------	-----------

Mechanical Characteristics

Mechanical Tests

Description	Tested Standard	Requirement/Value	According to Family Specification
-------------	-----------------	-------------------	-----------------------------------

Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	60 mm	IEC 60794-2-10
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	300 N (67 lbf)	IEC 60794-2-10
Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	100 N (22 lbf)	IEC 60794-2-10
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3	5 kN/m	IEC 60794-2-10

Temperature Range

Operating Temperature Range:	-40 °C to +70 °C
Installation Temperature Range:	-15 °C to +50 °C
Storage Temperature Range:	-40 °C to +70 °C

Standards

UL Rating/Flame Test:	Non-UL Rated
IEC Flammability:	IEC 60332-1-2
Reaction to Fire - Bundle Flame Test:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	10 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%
CPR Euroclass:	Eca
REACH:	Compliant
ISO/IEC Compliance:	IEC 60794-1-1
EU Directive 2011/65/EU (RoHS 2):	Compliant
UV/ Sunlight Protection:	Yes

History

Update and Revision:	Revision Number: 0.88 Revision Date: 04-10-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.