



**Product:** [GOCNE12](#) 

Outdoor OFC CLT (jelly filled): GLASS YARNS + CST + PE with 1 Tube of Ø3.3mm 12f MM OM4.

## Product Description

Outdoor optical fiber Central Loose Tube (jelly filled tube) cable with glass yarns as strength member, Corrugated Steel Tape armor and polyethylene outer jacket. Existing out of 1 Tube with a diameter of 3.3mm with 12 fibers MM OM4.

## Technical Specifications

### Product Overview

Construction Type:	Central Loose Tube
Environmental Space:	Outdoor
Suitable Applications:	For outdoor use in structured (data) wiring systems such as industrial backbone, campus backbone, building backbone (riser) and/or horizontal cabling. For outdoor use in networks for industrial, telecom, cable TV and/or broadcast. Easy to install in ducts, tunnels and trenches and/or tubes. Suitable for Direct Burial.

### Construction

#### Fiber Cable Construction

Fiber Type	Fiber Count	Subunit Color	Subunit Color 2
OM4	12	TIA coding (Gxxxxx.T): Natural	Europe coding (Gxxxxx.0): Natural

Fiber Color Coding:	TIA coding (Gxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua
Fiber Color Coding 2:	Europe coding (Gxxxxx.0): Red, Natural, Yellow, Blue, Green, Violet, Brown, Black, Orange, Aqua, Pink, White
Cable Core Water Tight:	Yes
Cable Core Water Blocking:	Waterblocking Glass Yarns + Tape
Bulk Cable Weight:	81 kg/km

### SubUnit Specifications

Number of Active Subunits:	1
Number of Subunit Positions:	1
Subunit Diameter:	3.3 mm
Subunit Waterblocking:	Gel Filled

### Jacket Specifications

Number of Jackets:	Single Jacket
Type of Armor:	Corrugated Steel Tape

### Outer Jacket Specifications

#### Outer Jacket

Material	Color	Nominal Diameter	Nominal Wall Thickness	Ripcord
PE - Polyethylene	Black	9.0 mm	1.55 mm	1

Table Notes:	Standard color: Black. Available colors: Black, Orange, Yellow, Turquoise, Erika Violet, Red, Blue, Green, Brown, Violet, Pink, Grey, White, Lime Green
--------------	---

### Optical Characteristics

Fiber Core Diameter:	50 µm
Max. Attenuation at 1300 nm:	0.9 dB/km

Max. Attenuation at 850 nm:	2.9 dB/km
-----------------------------	-----------

## Mechanical Characteristics

### Mechanical Tests

Description	Tested Standard	Requirement/Value	According to Family Specification
Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E6	180 mm	IEC 60794-3-10
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	180 mm	IEC 60794-3-10
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	2400 N (540 lbf)	IEC 60794-3-10
Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	800 N (180 lbf)	IEC 60794-3-10
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3	22 kN/m	IEC 60794-3-10
Cable Max. Crush Resistance Operation (Long Term)	IEC 60794-1-21-E3	11 kN/m	IEC 60794-3-10

### Temperature Range

Operating Temp Range:	-30 °C to +70 °C
Installation Temp Range:	-5 °C to +50 °C
Storage Temp Range:	-30 °C to +70 °C

### Standards

UL Rating/Flame Test:	Non-UL Rated
REACH:	Compliant
ISO/IEC Compliance:	IEC 60794
EU Directive 2011/65/EU (RoHS 2):	Compliant
UV/ Sunlight Protection:	Yes

### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	EAN
GOCNE12.002100	Black	Reel	2,100 m	8719605077509
GOCNE12.004100	Black	Reel	4,100 m	8719605155535

### History

Update and Revision:	Revision Number: 0.130 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.