



Product: [GUKBF08](#) 

Universal OFC : GLASS YARNS + CST + LSZH + PA + LSZH with 1 Tube of Ø4.2mm 8f SM OS2 G.657.A2. CPR Eca.

Product Description

Universal (Indoor/Outdoor) optical fiber cable with glass yarns as strength member, Corrugated Steel Tape (Full Rodent Protected) inner armor, Low Smoke Zero Halogen inner jacket, termite protection by polyamide layer and Low Smoke Zero Halogen outer jacket. Product feature: This cable has improved rodent protection by Corrugated Steel Tape (Full Rodent Protected), termite protection by polyamide layer and has Circuit Integrity properties. Existing out of 1 Tube with a diameter of 4.2mm with 8 fibers SM OS2 G.657.A2. CPR Euroclass Eca.

Technical Specifications

Product Overview

Construction Type:	Central Loose Tube
Environmental Space:	Indoor/Outdoor - Euroclass Eca
Suitable Applications:	For outdoor and indoor use in structured (data) wiring systems such as industrial backbone, campus backbone, building backbone (riser) and/or horizontal cabling. For outdoor and indoor use in networks for industrial, telecom, cable TV and/or broadcast. Easy to install in ducts, tunnels and trenches and/or tubes. Suitable for Direct Burial.

Construction

Fiber Cable Construction

Fiber Type	Fiber Grade acc. ITU-T	Fiber Count	Subunit Color
OS2	G.657A2	8	TIA coding (Gxxxxx.T): Natural

Fiber Color Coding:	TIA coding (Gxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black
Cable Core Water Tight:	Yes
Cable Core Waterblocking:	Waterblocking Glass Yarns + Tape
Bulk Cable Weight:	230 kg/km

SubUnit Specifications

Number of Active Subunits:	1
Number of Subunit Positions:	1
Fibers Per Subunit:	8
Subunit Diameter:	4.2 mm
Subunit Waterblocking:	Gel Filled

Jacket Specifications

Number of Jackets:	Triple Jacket
Type of Armor:	Corrugated Steel Tape

Outer Jacket Specifications

Outer Jacket

Material	Nominal Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)		No
Nylon		
LSZH - Low Smoke Zero Halogen (Flame Retardant)	13.6 mm	

Table Notes:	Standard color: Black. Available colors: Black, Orange, Yellow, Turquoise, Erika Violet, Red, Blue, Green, Brown, Violet, Pink, Grey, White, Lime Green
--------------	---

Optical Characteristics

Max. Attenuation at 1310 nm:	0.40 dB/km
Max. Attenuation at 1550 nm:	0.30 dB/km
Max. Attenuation at 1625 nm:	0.30 dB/km

Mechanical Characteristics

Mechanical Tests

Description	Tested Standard	Requirement/Value	According to Family Specification
Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E6	272 mm	IEC 60794-3-10
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	136 mm	IEC 60794-3-10
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	5700 N (1281 lbf)	IEC 60794-3-10
Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	1900 N (427 lbf)	IEC 60794-3-10
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3	22 kN/m	IEC 60794-3-10
Cable Max. Crush Resistance Operation (Long Term)	IEC 60794-1-21-E3	11 kN/m	IEC 60794-3-10

Temperature Range

Operating Temperature Range:	-30 °C to +70 °C
Installation Temperature Range:	-5 °C to +40 °C
Storage Temperature Range:	-30 °C to +70 °C

Standards

UL Rating/Flame Test:	Non-UL Rated
IEC Flammability:	IEC 60332-1-2
Reaction to Fire - Bundle Flame Test:	IEC 60332-3-22
Resistance to Fire - Circuit Integrity:	IEC 60331-25-E120
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	10 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4,3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%
CPR Euroclass:	Eca
REACH:	Compliant
ISO/IEC Compliance:	IEC 60794, ISO/IEC 11801-1
EU Directive 2011/65/EU (RoHS 2):	Compliant
UV/ Sunlight Protection:	Yes

History

Update and Revision:	Revision Number: 0.49 Revision Date: 09-17-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.