



Product: [GUSKCF08](#)

Universal bare fiber mini fiber cable with glass yarns as strength member and standard rodent protection. LSZH jacket 8f SM OS2 G.657.A2. CPR Cca.

Product Description

Universal (Indoor/Outdoor) bare fiber mini optical fiber cable with glass yarns as strength member and standard rodent protection. with Low Smoke Zero Halogen outer jacket. 8 fibers SM OS2 G.657.A2. CPR Euroclass Cca.

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | For indoor and outdoor use in structured (premises) wiring systems: building backbone (riser) and/or horizontal cabling (Fibre To The Desk). Support all computer network applications such as FDDI, Gigabit Ethernet and ATM. Easy to install in ducts and tunnels. |
|------------------------|--|

Fiber Specifications

| | |
|-------------------------|--|
| Fiber Type: | OS2 |
| Fiber Grade acc. ITU-T: | G.657.A2 |
| Fiber Count: | 8 |
| Fiber Color Coding: | TIA coding (Gxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black |

Cable Construction

| | |
|---------------------------|----------------------|
| Subunit Waterblocking: | Waterblocking Aramid |
| Cable Core Waterblocking: | Aramid Yarn |

Inner Jacket Specifications

| | |
|-----------|---|
| Material: | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
|-----------|---|

Outer Jacket Specifications

| | |
|------------------|---|
| Jacket Material: | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
| Nom. Diameter: | 4.3 mm (0.17 in) |

Optical Characteristics

| Wavelength | 1310 nm | 1550 nm | 1625 nm |
|------------------|------------|------------|------------|
| Max. Attenuation | 0.50 dB/km | 0.30 dB/km | 0.51 dB/km |

Mechanical Characteristics

Mechanical Tests

| Description | Tested Standard | Requirement/Value | According to Family Specification |
|---|--------------------|----------------------------------|-----------------------------------|
| Cable Min. Bend Radius Installation (Short Term) | IEC 60794-1-21-E6 | 86 mm | IEC 60794-2-20 |
| Cable Min. Bend Radius Operation (Long Term) | IEC 60794-1-21-E11 | 43 mm | IEC 60794-2-20 |
| Cable Max. Tensile Strength Installation (Short Term) | IEC 60794-1-21-E1 | 1200 N | IEC 60794-2-20 |
| Cable Max. Tensile Strength Operation (Long Term) | IEC 60794-1-21-E1 | 400 N | IEC 60794-2-20 |
| Cable Max. Crush Resistance Installation (Short Term) | IEC 60794-1-21-E3 | 5 kN/m | IEC 60794-2-20 |
| Cable Max. Crush Resistance Operation (Long Term) | IEC 60794-1-21-E3 | 3 kN/m | IEC 60794-2-20 |
| Cable Impact Resistance | IEC 60794-1-21-E4 | 10.0 J, 300 mm Radius, 3 Impacts | IEC 60794-2-20 |
| Waterblocking | IEC 60794-F5 | Pass | |

| | |
|--------------------|--------------------------|
| Bulk Cable Weight: | 20 kg/km (13 lbs/1000ft) |
|--------------------|--------------------------|

Temperature Range

| | |
|----------------------------------|-------------------|
| Installation Temperature Range: | 0 °C to +50 °C |
| Operating Temperature Range: | -10 °C to +55 °C |
| Storage Temperature Range: | -10 °C to +55 °C |
| Temperature Range Test Standard: | IEC 60794-1-22-F1 |

Standards and Compliance

| | |
|----------------------------------|--|
| Environmental Suitability: | Indoor/Outdoor - Euroclass Cca, Indoor, UV Resistance |
| Flammability / Reaction to Fire: | IEC 60332-1-2 |
| CPR Compliance: | CPR Euroclass: Cca-s1,d1,a1 |
| ISO/IEC Compliance: | IEC 60794ISO/IEC 11801-1, IEC 61034-2 - Smoke Density Min Transmittance = 60% |
| European Halogen Free Standards: | IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3 |
| European Directive Compliance: | EU CE Mark, EU Directive 2011/65/EU (RoHS 2) |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.3 Revision Date: 06-11-2025 |
|----------------------|--|

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.