



**Product:** [GUMX224](#) 

Universal tight buffered fiber + CST distribution cable LSZH jacket 24f MM OM2.

## Product Description

Universal (Indoor/Outdoor) tight buffered with Corrugated Steel Tape optical fiber distribution cable with Low Smoke Zero Halogen outer jacket. 24 fibers MM OM2.

## Technical Specifications

### Product Overview

|                        |  |
|------------------------|--|
| Construction Type:     | Distribution   |
| Environmental Space:   | Indoor/Outdoor - Euroclass Eca   |
| Suitable Applications: | For outdoor and indoor use in structured (data) wiring systems such as industrial backbone, campus backbone, building backbone (riser) and/or horizontal cabling. For outdoor and indoor use in networks for industrial, telecom, cable TV and/or broadcast. Support all computer network applications such as FDDI, Gigabit Ethernet and ATM. |

### Construction

#### Fiber Cable Construction

| Fiber Type | Fiber Count |
|------------|-------------|
| OM2        | 24          |

|                     |   |
|---------------------|---|
| Fiber Color Coding: | TIA coding (Gxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua. With Ringmark: BL, OR, GR, BR, GY, WT, RD, BK, YL, VT, PK, AQ |
|---------------------|---|

#### Buffer Specification

| Fiber Type | Buffer Construction | Buffer Material                                 | Buffer Diameter |
|------------|---------------------|---|-----------------|
| OM2        | Tight               | LSZH - Low Smoke Zero Halogen (Flame Retardant) | 0.9 mm          |

|                           |                           |
|---------------------------|---------------------------|
| Cable Core Water Tight:   | Yes                       |
| Cable Core Waterblocking: | Waterblocking Glass Yarns |
| Bulk Cable Weight:        | 199 kg/km                 |

### Jacket Specifications

|                    |                       |
|--------------------|-----------------------|
| Number of Jackets: | Double Jacket         |
| Type of Armor:     | Corrugated Steel Tape |

### Inner Jacket

|           |   |
|-----------|---|
| Material: | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
|-----------|---|

### Outer Jacket Specifications

#### Outer Jacket

| Material  | Nominal Diameter | Ripcord |
|---|------------------|---------|
| LSZH - Low Smoke Zero Halogen (Flame Retardant) | 14.5 mm          | Yes     |

|              |  |
|--------------|--|
| Table Notes: | Standard color: Orange. Available colors: Orange, Yellow, Turquoise, Erika Violet, Red, Blue, Green, Brown, Violet, Pink, Grey, White, Black, Lime Green |
|--------------|--|

### Optical Characteristics

|                              |           |
|------------------------------|-----------|
| Max. Attenuation at 1300 nm: | 0.9 dB/km |
| Max. Attenuation at 850 nm:  | 2.9 dB/km |

### Mechanical Characteristics

## Mechanical Tests

| Description   | Tested Standard    | Requirement/Value | According to Family Specification |
|---|--------------------|-------------------|-----------------------------------|
| Cable Min. Bend Radius Installation (Short Term)      | IEC 60794-1-21-E6  | 290 mm            | IEC 60794-2-20                    |
| Cable Min. Bend Radius Operation (Long Term)          | IEC 60794-1-21-E11 | 217.5 mm          | IEC 60794-2-20                    |
| Cable Max. Tensile Strength Installation (Short Term) | IEC 60794-1-21-E1  | 2500 N (562 lbf)  | IEC 60794-2-20                    |
| Cable Max. Tensile Strength Operation (Long Term)     | IEC 60794-1-21-E1  | 830 N (187 lbf)   |                                   |
| Cable Max. Crush Resistance Installation (Short Term) | IEC 60794-1-21-E3  | 22 kN/m           | IEC 60794-2-20                    |
| Cable Max. Crush Resistance Operation (Long Term)     | IEC 60794-1-21-E3  | 11 kN/m           | IEC 60794-2-20                    |

## Temperature Range

|                                 |                  |
|---------------------------------|------------------|
| Operating Temperature Range:    | -20 °C to +70 °C |
| Installation Temperature Range: | -5 °C to +50 °C  |
| Storage Temperature Range:      | -30 °C to +70 °C |

## Standards

|  |                            |
|--|----------------------------|
| UL Rating/Flame Test:                                      | Non-UL Rated               |
| IEC Flammability:  | IEC 60332-1-2              |
| Reaction to Fire - Bundle Flame Test:                      | IEC 60332-3-22             |
| IEC 60754-1 - Halogen Amount:                              | Zero                       |
| IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity: | 10 µS/mm                   |
| IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:           | 4.3                        |
| IEC 61034-2 - Smoke Density Min. Transmittance:            | 60%                        |
| CPR Euroclass:   | Eca                        |
| REACH:   | Compliant                  |
| ISO/IEC Compliance:  | IEC 60794, ISO/IEC 11801-1 |
| EU Directive 2011/65/EU (RoHS 2):                          | Compliant                  |
| UV/ Sunlight Protection:                                   | Yes                        |

## History

|                      |   |
|----------------------|---|
| Update and Revision: | Revision Number: 0.60 Revision Date: 09-17-2024 |
|----------------------|---|

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.