




Product: [H1001C1](#)

Life Cycle Status: Discontinued



H1001C1 - 50 Ohm Wireless Transmission Coax, H1000, RG8, 10 AWG Stranded BC, CU-Foil + 50% BC Braid, PE Jkt

Product Description

50 Ohm Wireless Transmission Coax, H1000, RG8, 10 AWG Stranded Bare Copper Conductor, PE Insulation, Copper foil + 50% Bare Copper Braid Shield, PE Jacket

Technical Specifications

Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

Construction Details

RG Type:	8
----------	---

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	10 AWG	Stranded	2.7 mm	BC - Bare Copper

Insulation

Element	Material	Nom. Insulation Diameter
Insulated Conductor	PE - Polyethylene (Foam)	7.15 mm (0.281 in)

Table Notes:	Centricity min. 85%
--------------	---------------------

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Tape	Bi-Laminate (Bare Copper+Poly)	100%
2	Braid	Bare Copper (BC)	50%

Outer Jacket

Material	Nom. Diameter
PE - Polyethylene	10.3 mm

Table Notes:	According to European Standard EN 50290-2-20
--------------	--

Electrical Characteristics

Regularity of Impedance:	Min. 46 dB
--------------------------	------------

Attenuation

Frequency	Nom. Attenuation
5 MHz	1 dB/100m
50 MHz	3.3 dB/100m
100 MHz	4.7 dB/100m
200 MHz	6.7 dB/100m
400 MHz	9.8 dB/100m
600 MHz	12.2 dB/100m
800 MHz	14.4 dB/100m
1000 MHz	16.3 dB/100m
1350 MHz	19.3 dB/100m

1750 MHz	22.5 dB/100m
2150 MHz	25.4 dB/100m
2400 MHz	27.1 dB/100m
5000 MHz	42.4 dB/100m
10000 MHz	66.4 dB/100m

Table Notes: Max. attenuation 10% higher

Electricals

Max. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
4.5 Ohm/km (1.4 Ohm/1000ft)	12 Ohm/km (3.7 Ohm/1000ft)	80 pF/m (24 pF/ft)	50 Ohm	83%

Screening

Frequency	Min. Screening Attenuation
30 - 1000 MHz	100 dB

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C To +70°C	-5°C To +50°C	-40°C To +70°C

Bend Radius

Stationary Min.
100 mm (3.9 in)

Bulk Cable Weight: 109 kg/km

Standards and Compliance

Environmental Suitability:	Outdoor
ISO/IEC Compliance:	IEC 61196
European Directive Compliance:	EU CE Mark

History

Update and Revision: Revision Number: 0.199 Revision Date: 07-29-2024

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.