



**Product:** [GUXTBD24](#)

Universal tight buffered OFC: GLASS YARNS (impr. rodent protection) LSZH jacket CPR B2ca. 24f MM OM3.

### Product Description

Universal (Indoor/Outdoor) tight buffered optical fiber cable with glass yarns as strength member and improved rodent protection with Low Smoke Zero Halogen outer jacket. CPR Euroclass B2ca. 24 fibers MM OM3.

### Technical Specifications

#### Product Overview

Construction Type:	Distribution
Environmental Space:	Indoor/Outdoor - Euroclass B2ca
Suitable Applications:	For outdoor and indoor use in structured (data) wiring systems such as industrial backbone, campus backbone, building backbone (riser) and/or horizontal cabling. For outdoor and indoor use in networks for industrial, telecom, cable TV and/or broadcast. Support all computer network applications such as FDDI, Gigabit Ethernet and ATM. Not suitable for blown installation.

#### Construction

##### Fiber Cable Construction

Fiber Type	Fiber Count
OM3	24

Fiber Color Coding:	TIA coding (Gxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua. With Ringmark: BL, OR, GR, BR, GY, WT, RD, BK, YL, VT, PK, AQ
---------------------	---

##### Buffer Specification

Fiber Type	Buffer Construction	Buffer Material	Buffer Diameter
OM3	Tight	LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.9 mm

Cable Core Water Tight:	Yes
Cable Core Water Blocking:	Waterblocking Glass Yarns
Bulk Cable Weight:	121 kg/km

#### Jacket Specifications

Number of Jackets:	Single Jacket
Type of Armor:	Non-Armored

#### Outer Jacket Specifications

##### Outer Jacket

Material	Nominal Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	10.6 mm	0

Table Notes:	Standard color: Orange. Available colors: Orange, Yellow, Turquoise, Erika Violet, Red, Blue, Green, Brown, Violet, Pink, Grey, White, Black, Lime Green
--------------	--

#### Optical Characteristics

Fiber Core Diameter:	50 µm
Max. Attenuation at 1300 nm:	1.0 dB/km
Max. Attenuation at 850 nm:	2.9 dB/km

#### Mechanical Characteristics

##### Mechanical Tests

Description	Tested Standard	Requirement/Value	According to Family Specification
Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E6	212 mm	IEC 60794-2-20
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	106 mm	IEC 60794-2-20
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	1210 N (272 lbf)	IEC 60794-2-20
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3	5 kN/m	IEC 60794-2-20
Cable Max. Crush Resistance Operation (Long Term)	IEC 60794-1-21-E3	3 kN/m	IEC 60794-2-20

## Temperature Range

Operating Temp Range:	-30 °C to +55 °C
Installation Temp Range:	-5 °C to +50 °C
Storage Temp Range:	-30 °C to +55 °C

## Standards

UL Rating/Flame Test:	Non-UL Rated
IEC Flammability:	IEC 60332-1-2
Reaction to Fire - Bundle Flame Test:	IEC 60332-3-24
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	10 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%
CPR Euroclass:	B2ca-s1,d1,a1
REACH:	Compliant
ISO/IEC Compliance:	IEC 60794
EU Directive 2011/65/EU (RoHS 2):	Compliant
UV/ Sunlight Protection:	Yes

## History

Update and Revision:	Revision Number: 0.24 Revision Date: 07-19-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.