



**Product:** [H2X120L](#)

MachFlex™ 610HH, 2 C 120.0mm<sup>2</sup> Str BC, LSZH Ins, LSZH Jkt, UL AWM Style 21115

## Product Description

MachFlex™ 610HH, 2 Conductor 120mm<sup>2</sup> Stranded Bare Copper, LSZH Insulation, LSZH Jacket , UL AWM Style 21115

## Technical Specifications

### Product Overview

Suitable Applications:	Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more. Utilizing LSZH material emits limited smoke and no halogen when exposed to high sources of heat. It can considerably reduce the amount and density of the smoke, toxic and corrosive gas emitted during a fire, enable easier evacuation as well as safer firefighting operations.
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	120mm <sup>2</sup>	Class 5	BC - Bare Copper	2

Conductor Count: 2

#### Insulation

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)

#### Color Chart

Color
Black #1
Black #2

#### Outer Jacket

Material	Nominal Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	21.2mm

### Electrical Characteristics

#### Conductor DCR

Max. Conductor DCR
0.161 Ohm/km

#### Voltage

Dielectric Withstand Voltage	Non-UL Description	Non-UL Voltage Rating
4000 V	IEC:	600/1000 V

### Temperature Range

Installation Temp Range:	-40°C to +80°C
Operating Temp Range:	-25°C to +70°C

### Mechanical Characteristics

Oil Resistance:	Yes
-----------------	-----

UV Resistance:	Yes
Bulk Cable Weight:	897 kg/km
Min. Bend Radius During Installation:	4 x OD
Min. Bend Radius During Operation:	15 x OD

## Standards

UL AWM Style Compliance:	AWM 21115
Other Specification:	EN 50525-3-11

## Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

## Suitability

Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2, IEC 60332-3-24 and IEC 60332-3-25
Other Flammability:	DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-3-24, IEC 60332-3-25
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	10 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60

## Part Number

### Variants

Item #	Color	Length
H2X120L 01050M	Black, RAL 9005	50 m
H2X120L 010100M	Black, RAL 9005	100 m
H2X120L 010200M	Black, RAL 9005	200 m
H2X120L G8U50M	Gray, RAL 7001	50 m
H2X120L G8U100M	Gray, RAL 7001	100 m
H2X120L G8U200M	Gray, RAL 7001	200 m

## History

Update and Revision:	Revision Number: 0.7 Revision Date: 12-15-2021
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.