



**Product:** [HD4B0020216FB](#)

Indoor/Outdoor Armored Hybrid Copper-Fiber Cable, OM4, 2 Breakout Fibers, 2.0mm Sub-units, #16-2c, CMR-OF

### Product Description

FX HYBRID INDOOR/OUTDOOR, OM4, BREAKOUT, 2 FIBERS, 02 x 16AWG, CMR-OF ALUMINUM INTERLOCKED ARMOR, SUB-UNIT 2.0MM (1F X 900UM), BLACK JACKET

### Technical Specifications

#### Product Overview

Suitable Applications:	Distributed Antenna Systems (DAS), Passive Optical Network (PON), Wireless Access Points (WAP), Security (Cameras)
------------------------	--

#### Fiber Specifications

Fiber Type:	OM4
Fiber Core Diameter:	50/125 $\mu$ m
Buffer Material:	PVC - Polyvinyl Chloride
Buffer Diameter:	900 $\mu$ m
Fiber Count:	2
Fiber Color Coding:	TIA-598-D

#### Fiber Construction

Subunit Strength Members:	Waterblocking aramid yarns
Fibers Per Subunit:	1
Nom. Jacket Diameter:	0.078 in. (2.0 mm)
Jacket Color:	Erika Violet

#### Conductor Specifications

AWG Size:	16
Number of Strands:	19x29
Conductor Type:	TC - Tinned Copper
Number of Conductors:	2
Insulation Material:	PVC
Nom. Insulation Diameter:	0.087 in. (2.2 mm)

#### Inner Jacket Specifications

Strength Member:	Waterblocking Aramid Yarns
Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.327 in (8.3 mm)
Color:	Erika Violet

#### Armor Specifications

Armor Type and Material:	AIA - Aluminum Interlock Armor
--------------------------	--------------------------------

#### Outer Jacket Specifications

Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.61 in (15.5 mm)

Color:	Black
Number of Ripcords:	1

#### Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.0 dB/km	1.0 dB/km
1 Gigabit Ethernet Performance	1000 m	550 m
10 Gigabit Ethernet Performance	550 m	--
Min. Effective Modal Bandwidth (EMB)	4700 MHz.km	--
Min. Overfilled Launch (OFL) Bandwidth	3500 MHz.km	500 MHz.km

#### Mechanical Characteristics

Min. Bend Radius During Installation:	20x Cable OD
Min. Bend Radius During Operation:	15x Cable OD
Max. Tensile Strength During Installation:	1335 N (300 lbf)
Max. Tensile Strength During Operation:	400 N (90 lbf)
Crush Resistance:	440 N/cm
Bulk Cable Weight:	166 lbs/kft (248 kg/km)

#### Temperature Range

Installation Temperature Range:	-10°C to +60°C
Operating Temperature Range:	-40°C to +70°C
Storage Temperature Range:	-40°C to +70°C

#### Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance, Burial
Sustainability:	CA Prop 65
NEC / UL Compliance:	CMR-OF
ICEA Compliance:	S-120-742
TIA/EIA Compliance:	ICEA S-120-742

#### History

Update and Revision:	Revision Number: 0.20 Revision Date: 02-15-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.