



Product: [HF12G0.75CP](#) 

MachFlex™ High Flex 350CP, 11+1G C 0.75mm² Str BC, PVC Ins, PUR Inner Jkt, TCBS, PUR Outer Jkt

Product Description

MachFlex™ High Flex Control 350CP, 11 Conductor + 1 Ground 0.75mm² Stranded Bare Copper, PVC Insulation, PUR Inner Jacket, Tinned Copper Braid Shield, PUR Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more. PUR jacket ensures the cable with excellent abrasion resistance and flex cycles more than 5 million would be ideally applied to drag chain and the frequently moving fields. Shielding would highly enable the cables be qualified with excellent immunity.
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	0.75 mm ²	Class 6	BC - Bare Copper	11
Ground	0.75 mm ²	Class 6	BC - Bare Copper	1

Conductor Count: 12

Insulation

Material
PVC - Polyvinyl Chloride

Color Chart

Color
Black #1
Black #2
Black #3
Black #4
Black #5
...
Black #11
Green/Yellow

Inner Jacket

Material
PUR - Polyurethane

Outer Shield

Type	Material
Braid	Tinned Copper (TC)

Outer Jacket

Material	Nominal Diameter
PUR - Polyurethane	12.9 mm

Electrical Characteristics

Conductor DCR

Max. Conductor DCR

19.5 Ohm/km

Voltage

Dielectric Withstand Voltage	Non-UL Description	Non-UL Voltage Rating
4000 V	IEC:	300/500 V

Temperature Range

Installation Temp Range:	-40°C to +80°C
Operating Temp Range:	-5°C to +70°C

Mechanical Characteristics

Oil Resistance:	Yes
UV Resistance:	Yes
Bulk Cable Weight:	252 kg/km
Min. Bend Radius During Installation:	4 x OD
Min. Bend Radius During Operation:	7.5 x OD
Min No. of Drag Chain Cycles:	≥ 5,000,000 Cycles (1MT Traverse Distance, 20cycles/min, 1.5m/s) ≥ 200,000 Cycles (5MT Traverse Distance, 20cycles/min, 1.5m/s)
Drag Chain Parameters:	1m Travel Distance, 20cycles/min, 1.5m/s

Standards

Other Specification: VDE 0285, VDE 0285-525-2-51

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2): Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
Other Flammability:	DIN VDE 0482-332-1-2, DIN EN 60332-1-2

Part Number

Variants

Item #	Color	Length
HF12G0.75CP 010305M	Black, RAL 9005	305 m
HF12G0.75CP 010500M	Black, RAL 9005	500 m
HF12G0.75CP 0101000M	Black, RAL 9005	1,000 m
HF12G0.75CP G8U305M	Gray, RAL 7001	305 m
HF12G0.75CP G8U500M	Gray, RAL 7001	500 m
HF12G0.75CP G8U1000M	Gray, RAL 7001	1,000 m

History

Update and Revision: Revision Number: 0.41 Revision Date: 12-15-2021

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.