



**Product:** [HF3G0.5CP](#) 

MachFlex™ High Flex 350CP, 2+1G C 0.5mm<sup>2</sup> Str BC, PVC Ins, PVC Inner Jkt, TCBS, PUR Outer Jkt

## Product Description

MachFlex™ High Flex Control 350CP, 2 Conductor + 1 Ground 0.5mm<sup>2</sup> Stranded Bare Copper, PVC Insulation, PVC Inner Jacket, Tinned Copper Braid Shield, PUR Outer Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more. PUR jacket ensures the cable with excellent abrasion resistance and flex cycles more than 5 million would be ideally applied to drag chain and the frequently moving fields. Shielding would highly enable the cables be qualified with excellent immunity.
------------------------	---

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Stranding Class	Material
Conductor(s)	2	0.5 mm <sup>2</sup>	Stranded	Class 6	BC - Bare Copper
Ground	1	0.5 mm <sup>2</sup>	Stranded	Class 6	BC - Bare Copper

#### Insulation

Element	Material	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	Black #1, Black #2
Ground	PVC - Polyvinyl Chloride	Yellow/Green

#### Outer Shield

Shield Type	Material
Braid	Tinned Copper (TC)

#### Inner Jacket

Material
PVC - Polyvinyl Chloride

#### Outer Jacket

Material
PUR - Polyurethane

Overall Cable Diameter (Nominal):	7.4 mm (0.29 in)
-----------------------------------	------------------

### Electrical Characteristics

#### Voltage

Voltage Rating
300/500 V (Max. Operating Voltage), 4000 V (Testing Voltage)

### Mechanical Characteristics

#### Temperature

Installation	Continuous Flexing
-40°C to +80°C (Fixed installation)	0°C to +70°C

## Bend Radius

Installation Min.	Flexing Min.
29.6 mm (1.17 in)	55.5 mm (2.19 in)

Table Notes:	Drag Chain Performance : 1m Travel Distance, Travel Speed 2m/s, Acceleration 4m/s <sup>2</sup> ≥ 5,000,000 Cycles; 3m Travel Distance, Travel Speed 3m/s, Acceleration 10m/s <sup>2</sup> ≥ 1,000,000 Cycles; 5m Travel Distance, Travel Speed 3m/s, Acceleration 10m/s <sup>2</sup> ≥ 200,000 Cycles
Bulk Cable Weight:	76 kg/km (51 lbs/1000ft)

## Standards and Compliance

Environmental Suitability:	Sunlight Resistance, UV Resistance, Oil Resistance - 70°C x 4h
Flammability / Reaction to Fire:	IEC 60332-1-2, DIN VDE 048233212, DIN EN 6033212
ISO/IEC Compliance:	IEC 60228
CENELEC Compliance:	EN 50290-2-22
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2)
Other Standard Compliance(s):	VDE 0285, EN 50525-2-51, VDE 0285-525-2-51, EN 50363-3, EN 50363-10-2, VDE 0295, BS 6360

## Product Notes

Notes:	General Reference Standards : VDE 0207-363-3, VDE 0207-363-10-2
--------	---

## History

Update and Revision:	Revision Number: 0.45 Revision Date: 11-28-2023
----------------------	---

## Part Numbers

### Variants

Item #	Color	Length
HF3G0.5CP 010100M	Black	100 m
HF3G0.5CP 010200M	Black	200 m
HF3G0.5CP 010300M	Black	300 m
HF3G0.5CP 006100M	Blue	100 m
HF3G0.5CP 006200M	Blue	200 m
HF3G0.5CP 006300M	Blue	300 m
HF3G0.5CP G8U100M	Gray, RAL 7001	100 m
HF3G0.5CP G8U200M	Gray, RAL 7001	200 m
HF3G0.5CP G8U300M	Gray, RAL 7001	300 m

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.