



**Product:** [IEA003](#)

DataTuff® 6A, 4 Bonded-Pr #23 Sol BC, FEP Ins, FEP Jkt, CMP, Extreme Temp

## Product Description

4 Bonded-Pair, U/UTP-Unshielded, Category 6A, Plenum, 23 AWG Solid Bare Copper, FEP Insulation, Patented X-Spline & EquiBlock™ Technologies, FEP Jacket, Sequential Markings at 2 Feet

## Technical Specifications

### Product Overview

Suitable Applications:	extreme temp, exposure to oil and gasoline, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a> .

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

#### Insulation

Material	
FEP - Fluorinated Ethylene Propylene	
Bonded-Pair:	Yes

#### Color Chart

Color
White & Blue
White & Orange
White & Green
White & Brown

#### Outer Jacket

Material	Nominal Diameter	Ripcord	Separator Material
FEP - Fluorinated Ethylene Propylene	0.270 in	No	Center Member (Patented X-Spline®), EquiBlock™ Barrier Technology

### Electrical Characteristics

#### Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance	Max DCR Unbalanced Between Pairs [%]
82 Ohm/km	3 %	5 %

#### Capacitance

Max. Capacitance Unbalance	Nom.Mutual Capacitance
45 pF/100m	17 pF/ft

#### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	65%

#### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	74.3 dB	72.3 dB	72.2 dB	70.2 dB	67.8 dB	64.8 dB	20.0 dB	105 +/- 10	115 +/- 15	67.0 dB	67.0 dB	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	61.5 dB	59.5 dB	55.8 dB	52.8 dB	23.0 dB	105 +/- 10	100 +/- 7	67.0 dB	66.2 dB	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	55.4 dB	53.4 dB	49.7 dB	46.7 dB	24.5 dB	100 +/- 22	100 +/- 7	67.0 dB	60.1 dB	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	59.3 dB	57.3 dB	53.4 dB	51.4 dB	47.8 dB	44.8 dB	25.0 dB	100 +/- 22	100 +/- 7	67.0 dB	58.2 dB	40.0 dB	15.0 dB
16 MHz	7.5 dB/100m	56.2 dB	54.2 dB	48.8 dB	46.8 dB	43.7 dB	40.7 dB	25.0 dB	100 +/- 22	100 +/- 7	67.0 dB	54.1 dB	38.0 dB	10.9 dB
20 MHz	8.4 dB/100m	54.8 dB	52.8 dB	46.4 dB	44.4 dB	41.8 dB	38.8 dB	25.0 dB	100 +/- 22	100 +/- 7	67.0 dB	52.2 dB	37.0 dB	9.0 dB
25 MHz	9.4 dB/100m	53.3 dB	51.3 dB	44.0 dB	42.0 dB	39.8 dB	36.8 dB	24.3 dB	100 +/- 22	100 +/- 7	67.0 dB	50.2 dB	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	51.9 dB	49.9 dB	41.4 dB	39.4 dB	37.9 dB	34.9 dB	23.6 dB	100 +/- 22	100 +/- 7	67.0 dB	48.3 dB	35.1 dB	5.1 dB
62.5 MHz	15.0 dB/100m	47.4 dB	45.4 dB	32.4 dB	30.4 dB	31.9 dB	28.9 dB	21.5 dB	100 +/- 22	100 +/- 7	65.6 dB	42.3 dB	32.0 dB	
100 MHz	19.1 dB/100m	44.3 dB	42.3 dB	25.2 dB	23.2 dB	27.8 dB	24.8 dB	20.1 dB	100 +/- 22	100 +/- 7	62.5 dB	38.2 dB	30.0 dB	
200 MHz	27.6 dB/100m	39.8 dB	37.8 dB	12.2 dB	10.2 dB	21.8 dB	18.8 dB	18.0 dB	100 +/- 22	100 +/- 7	58.0 dB	32.2 dB	27.0 dB	
250 MHz	31.1 dB/100m	38.3 dB	36.3 dB	7.3 dB	5.3 dB	19.8 dB	16.8 dB	17.3 dB	100 +/- 32	100 +/- 7	56.5 dB	30.2 dB	26.0 dB	
300 MHz	34.3 dB/100m	37.1 dB	35.1 dB	2.9 dB	0.9 dB	18.3 dB	15.3 dB	16.8 dB	100 +/- 32	100 +/- 7	55.3 dB	28.7 dB	25.2 dB	
350 MHz	37.2 dB/100m	36.1 dB	34.1 dB			16.9 dB	13.9 dB	16.3 dB	100 +/- 32	100 +/- 7	54.3 dB	27.3 dB	24.6 dB	
400 MHz	40.1 dB/100m	35.3 dB	33.3 dB			15.8 dB	12.8 dB	15.9 dB	100 +/- 32	100 +/- 7	53.5 dB	26.2 dB	24.0 dB	
450 MHz	42.7 dB/100m	34.5 dB	32.5 dB			14.7 dB	11.7 dB	15.5 dB	100 +/- 32	100 +/- 7	52.7 dB	25.1 dB	23.5 dB	
500 MHz	45.3 dB/100m	33.8 dB	31.8 dB			13.8 dB	10.8 dB	15.2 dB	100 +/- 32	100 +/- 7	52.0 dB	24.2 dB	23.0 dB	

Segregation class according EN50174-2: a

#### Voltage

Non-UL Voltage Rating

300 V

#### Temperature Range

Installation Temp Range: -40°C To +125°C

UL Temp Rating: 150°C

Storage Temp Range: -55°C To +150°C

Operating Temp Range: -55°C To +150°C

#### Mechanical Characteristics

Bulk Cable Weight: 42 lbs/1000ft

Max. Pull Tension: 40 lbs

Min. Bend Radius During Installation: 2.75 in

#### Standards

ISO/IEC Compliance: ISO/IEC 11801-1, IEC 61156-5

CPR Euroclass: Fca

Data Category: Category 6A

TIA/EIA Compliance: ANSI/TIA-568.2-D Category 6A

IEEE Compliance: IEEE 802.3bt Type 1, Type 2, Type 3, Type 4

NEMA Compliance: ANSI/NEMA WC-66

#### Applicable Environmental and Other Programs

Environmental Space: Indoor/Outdoor

EU Directive 2011/65/EU (RoHS 2): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU CE Mark:	No
EU REACH SVHC Compliance (yyyy-mm-dd):	2020-01-16
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LSOH, Toxicity Testing

UL Flammability:	CMP
------------------	-----

## Part Number

Non-Plenum Number:	IEA001
--------------------	--------

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0. Not Suitable for Direct Burial. Belden recommends using an entrance demarcation point when transitioning inside buildings with gel-filled OSP cables due to the cable design containing gel specific for wet outdoor environments. The suggested transition point is the REVConnect core coupler, part number RVACPKUBK-S1.
--------	---

## History

Update and Revision:	Revision Number: 0.104 Revision Date: 11-02-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.