




Product: [H125C00](#)



H125C00 - Broadband Coax, H125, 18 AWG Solid BC, CU-Foil + 35% BC Braid, PVC Jkt

Product Description

Broadband Coax, H125, 18 AWG Solid Bare Copper Conductor, PE Insulation, Copper Foil + 35% Bare Copper Braid Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Over-The-Air (OTA) antennas
------------------------	--

Construction Details

RG Type:	6
----------	---

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	18 AWG	Solid	1 mm	BC - Bare Copper

Insulation

Element	Material	Nom. Insulation Diameter
Insulated Conductor	PE - Polyethylene (Foam)	4.8 mm (0.19 in)

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Tape	Bi-Laminate (Bare Copper+Poly)	100%
2	Braid	Bare Copper (BC)	35%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	6.8 mm

Table Notes:	According to EN 50290-2-20
--------------	----------------------------

Electrical Characteristics

Regularity of Impedance:	Min. 40 dB
--------------------------	------------

Return Loss (RL)

Frequency	Min. Return Loss
5 - 470 MHz	23 dB
470 - 1000 MHz	20 dB
1000 - 2000 MHz	18 dB
2000-3000 MHz	16 dB

Table Notes:	In each frequency band, 3 peak values up to 4 dB lower are allowed
--------------	--

Attenuation

Frequency	Nom. Attenuation
5 MHz	1.4 dB/100m
50 MHz	4.3 dB/100m
100 MHz	6.1 dB/100m
200 MHz	8.6 dB/100m

400 MHz	12.3 dB/100m
600 MHz	15.2 dB/100m
800 MHz	17.7 dB/100m
1000 MHz	19.9 dB/100m
1350 MHz	23.5 dB/100m
1750 MHz	27 dB/100m
2150 MHz	30.2 dB/100m
2400 MHz	32.1 dB/100m

Table Notes:	Max. attenuation 10% higher
--------------	-----------------------------

Electricals

Max. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
23 Ohm/km (7.0 Ohm/1000ft)	20 Ohm/km (6.1 Ohm/1000ft)	55 pF/m (17 pF/ft)	75 Ohm	81%

Screening

Frequency	Min. Screening Attenuation
30 - 1000 MHz	75 dB

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C To +70°C	-5°C To +50°C	-40°C To +70°C

Bend Radius

Stationary Min.
70 mm (2.8 in)

Max. Pull Tension:	55 N (12 lbf)
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Eca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
CENELEC Compliance:	EN 50117-1, EN 50117-9-2, EN 50290-2-20
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.209 Revision Date: 05-31-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
H125C00.00B100	White	Flat Box	100 m	8719605086846
H125C00.00250	White	Reel	250 m	8719605086815
H125C00.00500	White	Reel	500 m	8719605086822