



Product: [KEYCONNECT SG FACEPLATES](#)

KeyConnect Single-Gang Faceplate

Product Description

KeyConnect Faceplate, Single Gang, Flush, Compatible with KeyConnect style modular jacks

Technical Specifications

Product Overview

Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, fiber and coax
------------------------	--

Physical Characteristics (Overall)

Height:	4.5 m
Width:	2.75
Depth:	0.26
Front Connection:	Flush
Packaging:	Individually packaged in a plastic bag.
Weight:	0.06 kg

Connectors

Materials

Material
Plastic - UL94V-0

Temperature Range

Installation Temperature Range:	-10 to 60°C
Storage Temperature Range:	-40 to 70°C
Operating Temperature Range:	-10 to 60°C

Mechanical Characteristics

Footprint/Type:	KeyConnect
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LSOH, Toxicity Testing

Safety Listing:	Bi-national Standard Listed
-----------------	-----------------------------

Related Part Numbers

Related Parts:	Compatible with KeyConnect-style Modular Jacks 10GX, CAT6+, CAT5E and KeyConnect-style Fiber and Coax Connectors
----------------	--

Variants

Item #	Color	Port Count
--------	-------	------------

AX102248	Almond	4 Port
AX102250	Almond	6 Port
AX103922	Almond	1 Port
AX103923	Almond	2 Port
AX103924	Almond	3 Port
AX104160	Black	1 Port
AX104161	Black	2 Port
AX104162	Black	3 Port
AX104163	Black	4 Port
AX104164	Black	6 Port
AX104464	Dark Gray	4 Port
AX102249	Electric White	4 Port
AX102251	Electric White	6 Port
AX102660	Electric White	1 Port
AX102661	Electric White	3 Port
AX104197	Ivory	2 Port
AX104198	Ivory	4 Port
AX104199	Ivory	6 Port
AX104565	Ivory	1 Port

Product Notes

Included Parts:	6-32 screw, carton label, clear window
Notes:	For proper installation refer to Installation Guide PX103826. Visit our web site at http://www.belden.com

History

Update and Revision:	Revision Number: 0.196 Revision Date: 03-04-2023
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.