



**Product:** [LC16N24B](#)

KeyConnect Loaded CAT6 Angled Patch Panel, 24 Port, 1U



## Product Description

KeyConnect Loaded CAT6 Angled Patch Panel, 24 Port, 1U, Black fitted with Bracket & bar and pre-loaded with Modular Jack

## Technical Specifications

### Physical Characteristics (Overall)

#### Color Chart

Color
Black

Port Count:	24 Port
Packaging:	Individually packaged in a cardboard box.

### Connectors

#### Materials

Description	Material
Panel	Steel
Front Connection – Jack	Copper Alloy with 50 $\mu$ Gold over Nickel
Rear Connection – Jack	Copper Alloy with Nickel Plating
Jack Body	Plastic – UL940V-2

### Construction and Dimensions

Max Capacity:	24 connectors
---------------	---------------

### Electrical Characteristics

Dielectric Strength:	1000 V RMS @ 60 Hz for 1 minute
Insulation Resistance:	500 MOhm Minimum
Contact Resistance (Switch Contact):	20 mOhm

#### Current

Max. Recommended Current [A]
1.5 A

### Temperature Range

Installation Temperature Range:	-10°C to +60°C
Storage Temperature Range:	-40°C to +70°C
Operating Temperature Range:	-10°C to +60°C

### Mechanical Characteristics

Footprint/Type:	KeyConnect
Plug /Jack Compatibility:	RJ45, RJ11

#### Termination Interface

Termination	Connection	Durabilities
-------------	------------	--------------

Front	Mated Type – Flush and Angled Connection	750 Cycles
Rear	Termination Type IDC Connection	20 Terminations

## Standards

Data Category:	Category 6
----------------	------------

## Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

## Product Notes

Included Parts:	T Bar for Jacks, 4 Screws (10X32), 4 Screws (12X24), 1 Installation Guide, 1 Ground Wire 24 AWG Kit (For Flat Panels Only)
-----------------	--

## History

Update and Revision:	Revision Number: 0.12 Revision Date: 04-08-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.