



Product: [H4G10CH](#) 

MachFlex™ 610CH, 3+1G C 10mm² Str BC, LSZH Ins, LSZH Inner Jkt, TCBS, LSZH Outer Jkt, UL AWM Style 21115

Product Description

MachFlex™ 610CH, 3 Conductor + 1 Ground 10mm² Stranded Bare Copper, LSZH Insulation, LSZH Inner Jacket, Tinned Copper Braid Shield, LSZH Outer Jacket, UL AWM Style 21115

Technical Specifications

Product Overview

Suitable Applications: Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more. Tinned copper braid shield ensures cables with excellent noise immunity. Utilizing LSZH material emits limited smoke and no halogen when exposed to high sources of heat. It can considerably reduce the amount and density of the smoke, toxic and corrosive gas emitted during a fire, enable easier evacuation as well as safer firefighting operations.

Physical Characteristics (Overall)

Conductor

| Element | AWG | Stranding | Material | No. of Conductors |
|--------------|--------------------|-----------|------------------|-------------------|
| Conductor(s) | 10 mm ² | Class 5 | BC - Bare Copper | 3 |
| Ground | 10 mm ² | Class 5 | BC - Bare Copper | 1 |

Conductor Count: 4

Insulation

| Material |
|---|
| LSZH - Low Smoke Zero Halogen (Flame Retardant) |

Color Chart

| Color |
|--------------|
| Black #1 |
| Black #2 |
| Black #3 |
| Green/Yellow |

Inner Jacket

| Material |
|---|
| LSZH - Low Smoke Zero Halogen (Flame Retardant) |

Outer Shield

| Type | Material |
|-------|--------------------|
| Braid | Tinned Copper (TC) |

Outer Jacket

| Material | Nominal Diameter |
|---|------------------|
| LSZH - Low Smoke Zero Halogen (Flame Retardant) | 19.90 mm |

Electrical Characteristics

Conductor DCR

| Max. Conductor DCR |
|--------------------|
| 1.91 Ohm/km |

Voltage

| Dielectric Withstand Voltage | Non-UL Description | Non-UL Voltage Rating |
|------------------------------|--------------------|-----------------------|
| 4000 V | IEC: | 600/1000 V |

Temperature Range

| | |
|--------------------------|----------------|
| Installation Temp Range: | -40°C to +80°C |
| Operating Temp Range: | 25°C to +70°C |

Mechanical Characteristics

| | |
|---------------------------------------|-----------|
| Oil Resistance: | Yes |
| UV Resistance: | Yes |
| Bulk Cable Weight: | 795 kg/km |
| Min. Bend Radius During Installation: | 6 x OD |
| Min. Bend Radius During Operation: | 20 x OD |

Standards

| | |
|--------------------------|---------------|
| UL AWM Style Compliance: | AWM 21115 |
| Other Specification: | EN 50525-3-11 |

Applicable Environmental and Other Programs

| | |
|-----------------------------------|-----|
| EU Directive 2011/65/EU (RoHS 2): | Yes |
|-----------------------------------|-----|

Suitability

| | |
|------------------------------------|-----|
| Suitability - Indoor: | Yes |
| Suitability - Oil Resistance: | Yes |
| Suitability - Outdoor: | Yes |
| Suitability - Sunlight Resistance: | Yes |

Flammability, LSOH, Toxicity Testing

| | |
|--|--|
| UL Flammability: | FT2 |
| IEC Flammability: | IEC 60332-1-2 |
| Other Flammability: | DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-3-24, IEC 60332-3-25 |
| IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity: | 10 µS/mm |
| IEC 60754-2 - Halogen Acid Gas Amount - Min. pH: | 4.3 |
| IEC 61034-2 - Smoke Density Min. Transmittance: | 60% |
| UL voltage rating: | 1000 V RMS |

Part Number

Variants

| Item # | Color | Length |
|-----------------|------------------|--------|
| H4G10CH 010305M | Black, RAL 9005 | 305 m |
| H4G10CH 010500M | Black, RAL 9005 | 500 m |
| H4G10CH G8U305M | Gray, RAL 7001 | 305 m |
| H4G10CH G8U500M | Gray, RAL 7001 | 500 m |
| H4G10CH 003305M | Orange, RAL 2003 | 305 m |
| H4G10CH 003500M | Orange, RAL 2003 | 500 m |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.36 Revision Date: 12-15-2021 |
|----------------------|---|

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.