



**Product:** [H7X4SY](#)

MachFlex™ 610 SY, 7C 4 mm<sup>2</sup> Str BC, PVC Ins, PVC Inner Jkt, GSW Brd, PVC Outer Jkt

## Product Description

MachFlex™ 610 SY Control Cable 7 Conductor 4 mm<sup>2</sup> Stranded Bare Copper, PVC Insulation, PVC Inner Jacket, Galvanized Steel Wire Braiding Armor, PVC Outer Jacket

## Technical Specifications

### Product Overview

|                        |   |
|------------------------|---|
| Suitable Applications: | Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more. Galvanized steel wire braid armor provides excellent mechanical protection. |
|------------------------|---|

### Construction Details

#### Conductor

| Element      | No. of Elements | Size              | Stranding | Stranding Class | Material         |
|--------------|-----------------|-------------------|-----------|-----------------|------------------|
| Conductor(s) | 7               | 4 mm <sup>2</sup> | Stranded  | Class 5         | BC - Bare Copper |

#### Insulation

| Element      | Material                 | Color Code   |
|--------------|--------------------------|--|
| Conductor(s) | PVC - Polyvinyl Chloride | Black #1, Black #2, Black #3, Black #4, Black #5, Black #6, Black #7 |

#### Inner Jacket

| Material                 |
|--------------------------|
| PVC - Polyvinyl Chloride |

#### Armor

| Armor Type & Material        |
|------------------------------|
| SWB - Steel Wire Braid Armor |

#### Outer Jacket

| Material                 |
|--------------------------|
| PVC - Polyvinyl Chloride |

|                                   |                    |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 19.1 mm (0.752 in) |
|-----------------------------------|--------------------|

### Electrical Characteristics

#### Voltage

| Voltage Rating  |
|---|
| 600 / 1000 V (Max. Operating Voltage), 4000 V (Testing Voltage) |

### Mechanical Characteristics

#### Temperature

| Operating                           | Installation                        |
|-------------------------------------|-------------------------------------|
| -5°C to +70°C (Occasional movement) | -40°C to +80°C (Fixed installation) |

#### Bend Radius

| Installation Min.   | Flexing Min.     |
|---------------------|------------------|
| 114.6 mm (4.512 in) | 382 mm (15.0 in) |

Bulk Cable Weight: 655 kg/km (440 lbs/1000ft)

## Standards and Compliance

|                                  |  |
|----------------------------------|--|
| Environmental Suitability:       | UV Resistance, Oil Resistance  |
| Flammability / Reaction to Fire: | IEC 60332-1-2, DIN VDE 048233212, DIN EN 6033212   |
| ISO/IEC Compliance:              | IEC 60228  |
| CENELEC Compliance:              | EN 50290-2-22  |
| European Directive Compliance:   | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2) |
| Other Standard Compliance(s):    | VDE 0295, DIN VDE 0207-363-4-1, IEC 60227-5, EN 50525-2-51, BS 6360                              |

## History

Update and Revision: Revision Number: 0.17 Revision Date: 03-05-2024

## Part Numbers

### Variants

| Item #         | Color          | Length |
|----------------|----------------|--------|
| H7X4SY 010100M | Black          | 100 m  |
| H7X4SY 010200M | Black          | 200 m  |
| H7X4SY 010300M | Black          | 300 m  |
| H7X4SY G8U100M | Gray, RAL 7001 | 100 m  |
| H7X4SY G8U200M | Gray, RAL 7001 | 200 m  |
| H7X4SY G8U300M | Gray, RAL 7001 | 300 m  |
| H7X4SY 003100M | Orange         | 100 m  |
| H7X4SY 003200M | Orange         | 200 m  |
| H7X4SY 003300M | Orange         | 300 m  |

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.