



Product: [H9G1.0](#)

MachFlex™ 610YY Control & Power Cable, 8+1G C 1.0mm² Str BC, PVC Ins, PVC Jkt

Product Description

MachFlex™ 610YY Control & Power Cable, 8 Conductor + 1 Ground 1.0mm² Stranded Bare Copper, PVC Insulation, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more.
------------------------	---

Construction Details

Element	No. of Elements	Size	Stranding	Stranding Class	Material
Conductor(s)	8	1 mm²	Stranded	Class 5	BC - Bare Copper
Ground	1	1 mm²	Stranded	Class 5	BC - Bare Copper

Element	Material	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	Black #1, Black #2, Black #3, Black #4, Black #5, Black #6, Black #7, Black #8
Ground	PVC - Polyvinyl Chloride	Yellow/Green

Outer Jacket

Material	
PVC - Polyvinyl Chloride	
Overall Cable Diameter (Nominal):	13.1 mm (0.516 in)

Electrical Characteristics

Voltage Rating
600/1000 V (Max. Operating Voltage), 4000 V (Testing Voltage)

Mechanical Characteristics

Operating	Installation
-5°C to +70°C(Occasional movement)	-40°C to +80°C(Fixed installation)

Installation Min.	Flexing Min.
52.4 mm (2.06 in)	196.5 mm (7.736 in)
Bulk Cable Weight:	227 kg/km (153 lbs/1000ft)

Standards and Compliance

Environmental Suitability:	Sunlight Resistance, UV Resistance, Oil Resistance - EN 50290-2-22 (TM54)
----------------------------	---

Flammability / Reaction to Fire:	IEC 60332-1-2, DIN VDE 048233212, DIN EN 6033212
ISO/IEC Compliance:	IEC 60228
CENELEC Compliance:	EN 50290-2-22
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2)
Other Standard Compliance(s):	IEC 60227-5, EN 50525-2-51, DIN VDE 0207-363-4-1, VDE 0295, BS 6360

History

Update and Revision:	Revision Number: 0.24 Revision Date: 11-27-2023
----------------------	---

Part Numbers

Variants

Item #	Color	Length
H9G1.0 010100M	Black	100 m
H9G1.0 010200M	Black	200 m
H9G1.0 010300M	Black	300 m
H9G1.0 006100M	Blue	100 m
H9G1.0 006200M	Blue	200 m
H9G1.0 006300M	Blue	300 m
H9G1.0 G8U100M	Gray, RAL 7001	100 m
H9G1.0 G8U200M	Gray, RAL 7001	200 m
H9G1.0 G8U300M	Gray, RAL 7001	300 m

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.