



Product: [HD4D0020212RJ](#) 

HYBRID INDOOR/OUTDOOR OM4 DISTRIBUTION 2 FIBERS 04 X 12AWG
CL3R-OF 4.7MM SUB X 900µm

Product Description

FX HYBRID INDOOR/OUTDOOR, OM4, DISTRIBUTION, 2 FIBERS, 04 X 12AWG, CL3R-OF, 4.7MM SUB X 900µm, BLACK

Technical Specifications

Product Overview

Suitable Applications:	Distributed Antenna Systems (DAS), Passive Optical Network (PON), Wireless Access Points (WAP), Security (Cameras)
------------------------	--

Fiber Specifications

Fiber Type:	OM4
Fiber Core Diameter:	50/125 µm
Fiber Buffer Material:	PVC - Polyvinyl Chloride
Fiber Buffer Diameter:	900 µm
Fiber Count:	2
Fiber Color Code:	TIA-598-D

Fiber Construction

Fiber SubUnit Strength Members:	Waterblocking aramid yarns
Jacket Material:	PVC - Polyvinyl Chloride
Nominal Jacket Diameter:	0.184" (4.7 mm)
Jacket Color Fiber Unit:	Erika Violet

Conductor Specifications

AWG Size:	14
Number of Conductors:	2
Insulation Material:	PVC
Nom. Insulation Diameter:	0.118" (3.0 mm)

Outer Jacket Specifications

Strength Member:	Fiberglass Yarns
Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.364" (9.2 mm)
Outer Jacket Color:	Black
Outer Jacket Ripcord:	1

Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.0 dB/km	1.0 dB/km
10 Gigabit Ethernet Performance	550 m	--
Min. Effective Modal Bandwidth (EMB)	4700 MHz-km Min	--
Min. Overfilled Launch (OFL) Bandwidth	3500 MHz-km Min	500 MHz-km Min

Mechanical Characteristics

Minimum Bend Radius During Installation:	15 x cable OD
--	---------------

Minimum Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	600 lbf (2670 N)
Max. Tensile Strength During Operation:	180 lbf (800 N)
Crush Resistance:	220 N/cm

Temperature Range

Installation Temperature Range:	-10°C to +60°C
Operating Temperature Range:	-40°C to +70°C
Storage Temperature Range:	-40°C to +70°C

Standards and Compliance

NEC / UL Compliance:	CL3R-OF
----------------------	---------

History

Update and Revision:	Revision Number: 0.6 Revision Date: 04-23-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.