

Product: [MFSBMxyzzzMLMN](#) 



FiberExpress MPO Assembly, Male To Male, Single Mode OS2, ULL, LSZH, No Pulling Eye, Yellow Jacket, Light Version

Product Description

FiberExpress MPO Assembly, Male To Male, Single Mode OS2, ULL, LSZH, No Pulling Eye, Yellow Jacket, Light Version

Technical Specifications

Product Overview

Suitable Applications:	Data Centers, Main Equipment Rooms, Telecommunications Rooms
------------------------	--

Fiber Specifications

Fiber Type:	OS2
Fiber Count:	12

Physical Specifications

Connectors

Description	Housing Color	Boot Color
Connector A (Inside End)	Green	Black
Connector B (Outside End)	Green	Black

Assembly Cable

Jacket Color
Yellow

Optical Characteristics

Fiber Connector Performance

Max. Insertion Loss	Min. Return Loss
0.35 dB	60 dB

Mechanical Characteristics

Minimum Bend Radius During Installation:	20 x OD
Minimum Bend Radius During Operation:	10 x OD
Crush Resistance:	500 N/100mm (Short Term), 100 N/100mm (Long Term)

Temperature Range

Operating Temperature Range:	-20°C to +60°C
Storage Temperature Range:	-20°C to +60°C

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2
TIA/EIA Compliance:	TIA 568.3-D

ISO/IEC Compliance:	ISO/IEC 11801IEC 61754-7
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2)

Product Notes

Related Parts:	FiberExpress Manager Modules and FiberExpress Ultra Frames and Cassettes,Pre loaded fiber tray assemblies.
Notes:	Outer Jacket Material: LSZH - Low Smoke Zero Halogen (Flame Retardant). The sixth letter X represents polarity: A: Type-A, B: Type-B, C: Type-C; The seventh letter Y represents numbers of connector on both side: 1: 1 Connector, 2: 2 Connectors, 3: 3 Connectors, 4: 4 Connectors, 6: 6 Connectors, 8: 8 Connectors, D: 12 Connectors; The eighth to the tenth letters ZZZ represents length. Tensile Strength : 220 N (Short Term), 66 N (Long Term).

History

Update and Revision:	Revision Number: 0.2 Revision Date: 08-05-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.