



Product: [MSC013](#)

MachFlex™ SERVO Classic 610BCY, 3C+1G 150mm² Str BC, PP Ins, OS + TC Brd, PVC Jkt

Product Description

MachFlex™ SERVO Classic 610BCY, 3 Conductor + 1 Ground 150mm² Stranded Bare Copper, PP Insulation, Overall Aluminum Foil Plus Tinned Copper Braid Shield, PVC Outer Jacket, 1000V Flexible SERVO Motor Supply Cable

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | Designed for connecting frequency converter and motor. Cable applications include heavy industry, chemical industry and paper industry in dry, damp or wet interiors. This type of cables suitable for plant engineering both of static or flexible use. Double screened power cable for large servo drive systems with high electrical load. |
|------------------------|---|

Construction Details

Conductor

| Element | No. of Elements | Size | Stranding | Stranding Class | Material |
|--------------|-----------------|-----------|-----------|-----------------|------------------|
| Conductor(s) | 3 | 150.0 mm² | Stranded | Class 5 | BC - Bare Copper |
| Ground | 1 | 150.0 mm² | Stranded | Class 5 | BC - Bare Copper |

Insulation

| Element | Material | Color Code |
|--------------|--------------------|--------------------|
| Conductor(s) | PP - Polypropylene | Brown, Black, Gray |
| Ground | PP - Polypropylene | Yellow/Green |

Outer Shield

| Shield Type | Material | Coverage |
|-------------|-------------------------|----------|
| Tape | Bi-Laminate (Alum+Poly) | 100% |
| Braid | Tinned Copper (TC) | 70% |

Outer Jacket

| Material |
|--------------------------|
| PVC - Polyvinyl Chloride |

| | |
|-----------------------------------|-------------------|
| Overall Cable Diameter (Nominal): | 55.9 mm (2.20 in) |
|-----------------------------------|-------------------|

Electrical Characteristics

Voltage

| UL Voltage Rating | Voltage Rating |
|---------------------------------|---|
| 1000 V (Max. Operating Voltage) | 600/1000 V (Max. Operating Voltage), 4000 V (Testing Voltage) |

Mechanical Characteristics

Temperature

| Operating | Installation |
|------------------------------------|------------------------------------|
| -5°C to +80°C(Occasional movement) | -40°C to +80°C(Fixed installation) |

Bend Radius

| Installation Min. | Flexing Min. |
|---------------------|---------------------|
| 223.6 mm (8.803 in) | 838.5 mm (33.01 in) |

| | |
|--------------------|------------------------------|
| Bulk Cable Weight: | 6750 kg/km (4540 lbs/1000ft) |
|--------------------|------------------------------|

Standards and Compliance

| | |
|----------------------------------|--|
| Environmental Suitability: | Sunlight Resistance, UV Resistance, Oil Resistance - 70°C x 4h |
| Flammability / Reaction to Fire: | VW-1, FT1, IEC 60332-1-2, DIN VDE 0482-332-1-2, DIN EN 60332-1-2 |
| AWM Compliance: | AWM 2570 |
| CENELEC Compliance: | EN 50290-2-25, EN 50363-4-1 |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2) |

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.78 Revision Date: 07-05-2024 |
|----------------------|---|

Part Numbers

Variants

| Item # | Color | Length |
|----------------|--------------------|--------|
| MSC013 368100M | Clear, Transparent | 100 m |
| MSC013 368200M | Clear, Transparent | 200 m |
| MSC013 368300M | Clear, Transparent | 300 m |

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.