



Product: [NH50115FUA](#) 

DataTuff™ Industrial Ethernet CAT5e 4x2x22AWG/1 F/UTP Fire Resistant

Product Description

DataTuff™ Industrial Ethernet CAT5e 4x2x22AWG/1 F/UTP Fire Resistant

Technical Specifications

Product Overview

Suitable Applications:	This Category 5e Cable is a cable standard for Gigabit Ethernet, capable to continue transmitting data even when being directly attacked by fire.
------------------------	---

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
22 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PE - Polyethylene	1.23 mm (0.0484 in)	Blue & White with Blue Strips, Orange & White with Orange Strips, Green & White with Green Strips, Brown & White with Brown Strips	Fire Protection Barrier: Mica glass Tape(MGT), Twist Direction = S

Inner Shield

Notes
All 4 Pairs laid up together over a cross filler & binded by Fire Protection Barrier: Mica Glass Tape(MGT)

Outer Jacket

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)

Overall Cable Diameter (Nominal):	10.60 mm (0.4173 in)
-----------------------------------	----------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Nom. Characteristic Impedance
54.3 Ohm/km @ 20 Deg. C	100 Ohm

Delay

Max. Delay Skew
45 ns/100m

Voltage

Voltage Rating
60 V

Mechanical Characteristics

Temperature

Operating
-40°C to + 60°C

Standards and Compliance

Environmental Suitability:	UV Resistance, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-22, IEC 60331-23
AWM Compliance:	AWM 21130
Data Category:	Category 5e
TIA/EIA Compliance:	TIA 568
Other Standard Compliance(s):	BS EN 50289-4-16

History

Update and Revision:	Revision Number: 0.12 Revision Date: 02-26-2026
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.