



Product: [NH50116UFA](#)

DataTuff™ Industrial Ethernet CAT6 4X2X23AWG/1 U/FTP SWA Fire Resistant

Product Description

23 AWG solid bare copper conductors, Polyethylene insulation, Mica Glass Tape Fire Protection, Individual Shielded Pair (U/FTP), Central Drain Wire, Mica Glass Tape, LSZH Inner Jacket, SWA, LSZH Jacket

Technical Specifications

Product Overview

Suitable Applications:	Industrial Ethernet Cat 6 connection with Fire Resistant capability
------------------------	---

Construction Details

Conductor

Element	Size	Stranding	Material	No. of Pairs	No. of Elements
Conductor(s)	23 AWG	Solid	BC - Bare Copper	4	8

Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PE - Polyethylene	1.58 mm (0.0622 in)	Blue & White with Blue Strip, Orange & White with Orange Strip, Green & White with Green Strip, Brown & White with Brown Strip	Fire Protection Barrier: Mica glass Tape(MGT)

Inner Shield

Element	Shield Type	Material	Drainwire Type	Notes
Individual Shielded Pair	Tape	Bi-Laminate (Alum+Poly)	26 AWG (Solid) TC	Fire Protection Barrier: Mica Glass Tape(MGT)

Inner Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	11.80 mm (0.4646 in)

Armor

Armor Type & Material
SWA - Steel Wire Armor

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	15.30 mm (0.6024 in)

Electrical Characteristics

Electricals	
Max. Conductor DCR	Nom. Characteristic Impedance
73.2 Ohm/km @ 20 Deg. C	100 Ohm
Delay	
Max. Delay Skew	
45 ns/70m	
High Frequency	

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]
4	3.8 dB/70m	66.3	63.3	56.0	53.0	23.0
10	6.0 dB/70m	60.3	57.3	48.0	45.0	25.0
20	8.5 dB/70m	55.8	52.8	42.0	39.0	25.0
25	9.6 dB/70m	54.3	51.3	40.0	37.0	24.3
31.25	10.7 dB/70m	52.9	49.9	38.1	35.1	23.6
62.5	15.5 dB/70m	48.4	45.4	32.1	29.1	21.5
100	19.9 dB/70m	45.3	42.3	28.0	25.0	20.1
200	29.1 dB/70m	40.8	37.8	22.0	19.0	18.0
250	33.0 dB/70m	39.3	36.3	20.0	17.0	17.3

Voltage

UL Voltage Rating
60 V

Mechanical Characteristics

Temperature

Operating
-40°C To +80°C

Standards and Compliance

Environmental Suitability:	UV Resistance, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-22, IEC 60331-23
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	IEC 61156-5, IEC 61034-2 - Smoke Density Min Transmittance = 60%
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = 0.50%, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3

History

Update and Revision:	Revision Number: 0.2 Revision Date: 09-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.