



**Product:** [NN00098](#)

Category 3 Cable, 100 Pair, U/UTP, LSZH Armoured Outdoor

### Product Description

Category 3 Premise Horizontal Cable (16MHz), 100-pair, 24 AWG, HDPE insulation, U/UTP, jelly filled cable core, PE inner jacket, Armouring, LSZH jacket

### Technical Specifications

#### Product Overview

Suitable Applications:	Backbone cable; Support current and future Category 3 applications, suitable for outdoor use
------------------------	----------------------------------------------------------------------------------------------

#### Construction Details

##### Conductor

Size	Stranding	Material	No. of Pairs
24 AWG	Solid	BC - Bare Copper	100

##### Insulation

Material	Nom. Insulation Diameter	Color Code	Notes
PE - Polyethylene	1 mm (0.039 in)	White & Blue, White & Orange, White & Green, White & Brown, White & Grey, Red & Blue, Red & Orange, Red & Green, Red & Brown, Red & Grey, Black & Blue, Black & Orange, Black & Green, Black & Brown, Black & Grey, Yellow & Blue, Yellow & Orange, Yellow & Green, Yellow & Brown, Yellow & Grey, Violet & Blue, Violet & Orange, Violet & Green, Violet & Brown, Violet & Grey	HDPE
		Blue, Orange, Green, Brown	

Table Notes:	Telecom Color Order
--------------	---------------------

##### Cable Core

Description
4 units of 25 pairs filled with jelly compound and covered with a crepe paper

##### Inner Jacket

Material	Nom. Diameter	Color
PE - Polyethylene	24.2 mm (0.953 in)	Black

##### Outer Shield

Shield Type	Material
Tape	EquiBlock®

##### Armor

Armor Type & Material
DST - Double Steel Tape

Table Notes:	2 FE/ZN tapes spirally wrapped
--------------	--------------------------------

##### Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	30.5 mm (1.20 in)

Overall Cable Diameter (Nominal):	30.5 mm (1.20 in)
-----------------------------------	-------------------

### Electrical Characteristics

#### Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
93.8 Ohm/km	66 pF/m (20 pF/ft)	330 pF/100m	100 Ohm

#### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. SRL (Structural Return Loss) [dB]
0.772	2.2 dB/100m	45	43	12
1	2.6 dB/100m	44	41	12
4	5.6 dB/100m	34	32	12
8	8.5 dB/100m	29	27	12
10	9.7 dB/100m	28	26	12
16	13.1 dB/100m	25	23	10

#### Voltage

Voltage Rating
72 V DC

## Mechanical Characteristics

#### Temperature

Operating	Installation
-30°C to +60°C	0°C To +50°C

#### Bend Radius

Stationary Min.	Installation Min.
152.5 mm (6.004 in)	457.5 mm

Bulk Cable Weight: 1160 kg/km

## Standards and Compliance

Environmental Suitability:	Outdoor
Data Category:	Category 3
ISO/IEC Compliance:	ISO/IEC 11801-1
European Directive Compliance:	EU CE Mark

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system.
--------	----------------------------------------------------------------------------------------------------------------------------------

## History

Update and Revision:	Revision Number: 0.236 Revision Date: 09-04-2024
----------------------	--------------------------------------------------

## Part Numbers

#### Variants

Item #	Color	Putup Type	Length	EAN
NN00098.00500	Black	Reel	500 m	8719605103512
NN00098.001000	Black	Reel	1,000 m	8719605103505

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.