




Product: [IAF-240 - Essential](#) 

Belden IAF-240 Industrial Firewall with Essential Edition Subscription (3-year)

Product Description

The Belden IAF-240 Industrial Firewall is designed for critical infrastructure and Industry 4.0 applications with four (4) Gigabit Ethernet ports (all RJ45), extended operating temperature range, hazardous location approvals, a quad-core ARM64 CPU, 4 GB LPDDR4 RAM, and 64 GB eMMC storage. This includes a 3-year Essential Edition subscription with advanced firewall, VPN, and edge computing capabilities.

Technical Specifications

Product description

Type:	IAF-240 - ESSENTIAL
Name:	IAF-240 - ESSENTIAL
Part Number:	942 355-001
Port type and quantity:	4 x GbE RJ45 ports
Port Speed:	10/100/1000 Mbit/s RJ45

More Interfaces

Power supply/signaling contact:	1 x plug-in terminal block, 10-pin
USB interface:	1 x USB 2.0 port
Serial Interface:	1 x RJ45 port (RS-232, RS-422, RS-485)
Power Supply:	1 x plug-in terminal block, 10-pin

Hardware

CPU:	NXP i.MX 8M Mini ARMv8 64-bit Cortex-A53 @ 1.6GHz (quad core)
Encryption:	TPM 2.0 (Trusted Platform Module)
Memory:	LPDDR4 4 GB
Storage:	64 GB eMMC storage

Power requirements

Operating Voltage:	Dual 12- 24 V DC
Power consumption:	Minimum – 2.5W, Maximum – 12W

Security features

Multipoint VPN:	IPsec (IKE v2), OpenVPN, WireGuard, WebVPN
-----------------	--

Service

Protocols:	IPv4, IPv6, NTP, VRRP, SNMPv3, PPPoE, DHCP, DNS, DynDNS, SSH, SSL
------------	---

Software

Management:	Web-based admin dashboard expandable with widgets, Cloud-based Firewall Management Software, High Availability (Configuration Synchronisation, Status Synchronisation, VRRP Virtual IPs), VLAN, Bash, Python Script Support, Quality of Service (QoS), SNMPv3, CRON Jobs, UPnP & NAT-PMP, Setup Wizard
Security:	Stateful Packet Inspection Firewall (Packet Filtering, Port Filtering), Firewall Learning Mode, Access Control Lists, Certification Management, Let's Encrypt Support, Network Objects, Application Control, eXpress Data Path
Routing:	Layer 3, Layer 2 Bridging, Network Address Translation (NAT), SNAT, DNAT, BiNAT
Application Support and Management:	Docker Container

Ambient conditions

MTBF (Telecordia SR-332 Issue 4) @ 25°C:	309,149 hours
Operating temperature:	-40-+70 °C
Storage/transport temperature:	-40-+85 °C
Relative humidity (non-condensing):	5-95 %

Mechanical construction

Dimensions (WxHxD):	48 x 137 x 105 mm
Weight:	613 g
Housing Material:	Aluminum with DIN clip
Mounting:	DIN Rail 35 mm
Protection class:	IP30
Protection Degree / IP Rating**:	IP30

Approvals

Basis Standard:	CE, FCC
Safety of industrial control equipment:	UL 61010
Hazardous locations:	ANSI/UL 121201 Class 1 Div. 2 – Haz. Loc, ATEX-114 Category 3G (Zone 2)

Reliability

Guarantee:	60 months (please refer to the terms of guarantee for detailed information)
Warranty:	5 Years

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com/index.html
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.5 Revision Date: 08-29-2025
----------------------	--

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.