



Product: [IBDN25P](#)

Category 5e Backbone Cable, 25 Pair, U/UTP, CMP

### Product Description

Category 5e Premise Backbone Cable (100MHz), 25 Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, PVC-LS Jacket

### Technical Specifications

#### Product Overview

Suitable Applications:	Premise Backbone Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
------------------------	---

#### Construction Details

##### Conductor

Size	Stranding	Material	No. of Pairs
24 AWG	Solid	BC - Bare Copper	25

##### Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	Western Electric (Non-Striped)

##### Outer Jacket

Material	Nom. Diameter	Ripcord
FEP - Fluorinated Ethylene Propylene	0.478 in (12.1 mm)	Yes

Overall Cable Diameter (Nominal):	0.478 in (12.1 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	330 pF/100m

##### Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100m	72%

##### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. RL (Return Loss) [dB]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	62.3	20.0	100 ± 15%
4	4.1 dB/100m	53.3	23.0	100 ± 15%
8	5.8 dB/100m	48.8	24.5	100 ± 15%
10	6.5 dB/100m	47.3	25.0	100 ± 15%
16	8.2 dB/100m	44.3	25.0	100 ± 15%
20	9.3 dB/100m	42.8	25.0	100 ± 15%
25	10.4 dB/100m	41.3	24.3	100 ± 15%
31.25	11.7 dB/100m	39.9	23.6	100 ± 15%
62.5	17.0 dB/100m	35.4	21.5	100 ± 15%
100	22.0 dB/100m	32.3	20.1	100 ± 15%

##### Voltage

<b>UL Voltage Rating</b>
300 V (CMP)

## Mechanical Characteristics

### Temperature

UL Temperature	Operating	Installation	Storage
60°C	-40°C To +60°C	0°C To +60°C	-40°C To +60°C

### Bend Radius

Stationary Min.	Installation Min.
4.5 in (110 mm)	8.75 in (222 mm)

Max. Pull Tension:	150 lbs (68 kg)
Bulk Cable Weight:	137 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-90-661
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
Third Party Performance Verification:	Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	IBDN25R

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage/Meter Markings.
--------	--

## History

Update and Revision:	Revision Number: 0.475 Revision Date: 04-29-2024
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
IBDN25P 008CUT	Gray	Cut to Length		612825061885
IBDN25P 008CUT	Gray	Cut to Length	1 ft	612825061885
IBDN25P 0081000	Gray	Reel	1,000 ft	612825061892
IBDN25P 0081000	Gray	Reel	1,000 ft	612825061892

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.