

Product: [OZD Profi G12DE ATEX 1, Profibus LWL-Rep](#) 



Interface converter electrical/optical for PROFIBUS networks; repeater function; in stainless steel cabinet; approvals for protection zones 1,21, 2 and 22

Product Description

Interface converter electrical/optical for PROFIBUS networks; repeater function; in stainless steel cabinet; approvals for protection zones 1,21, 2 and 22

Technical Specifications

Product description

Type:	OZD Profi G12DE ATEX 1, Profibus LWL-Rep
Name:	OZD Profi G12DE ATEX 1, Profibus LWL-Rep
Description:	Interface converter electrical/optical for PROFIBUS networks; repeater function; in stainless steel cabinet; approvals for protection zones 1,21, 2 and 22
Part Number:	943883321
Port type and quantity:	2 x optical: 4 sockets BFOC 2.5 (STR); 1 x electrical: Ex-e single clamp
Signal Type:	PROFIBUS (DP-V0, DP-V1, DP-V2 und FMS)

More Interfaces

Power Supply:	Ex-e single clamp
Signaling contact:	Ex-e single clamp

Network size - length of cable

Multimode fiber (MM) 50/125 µm:	3000 m, 13 dB link budget at 860 nm; A = 3 dB/km
Multimode fiber (MM) 62.5/125 µm:	3000 m, 15 dB link budget at 860 nm; A = 3.5 dB/km

Power requirements

Current consumption:	max. 200 mA
Input voltage range:	-7 V ... +12 V
Operating Voltage:	18 ... 32 VDC, typ. 24 VDC
Power consumption:	4.8 W
Redundancy functions:	HIPER-Ring (ring structure), redundand 24 V infeed

Power Output

Output voltage/output current (pin6):	5 VDC +5%, -10%, short circuit-proof/90 mA
---------------------------------------	--------------------------------------------

Ambient conditions

Operating temperature:	-20-+55 °C
Storage/transport temperature:	-40-+80 °C
Relative humidity (also condensing):	10-100 %

Mechanical construction

Dimensions (WxHxD):	230 x 219 x 108 mm
Weight:	3.7 kg
Housing Material:	stainless steel
Mounting:	screw mounting on the mounting plate
Protection class:	IP66

Approvals

Hazardous locations:	ATEX Zone 1
----------------------	-------------

Scope of delivery and accessories

Scope of delivery:	device, start-up instructions
--------------------	-------------------------------

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.