



**Product:** [OpEdge-4D](#) 

## Industrial Edge Gateway Device for DIN Rail Mounting

### Product Description

OpEdge-4D is a more cost-effective choice for applications that have lower computing requirements and provides robust edge computing power in a more compact design. With multiple hazardous location approvals, OpEdge-4D can operate in harsh environments.

### Technical Specifications

#### Product description

Type:	OpEdge-4D
Part Number:	942332003
Port type and quantity:	4 x Gigabit Ethernet RJ45 LAN
Port Speed:	10/100/1000 Mbit/s RJ45

#### More Interfaces

USB interface:	1 x USB 2.0 socket to connect an approved USB storage device
Serial Interface:	1 x RJ45 port (serial tunneling & encapsulation; RS232/422/485)
Power Supply:	1 x plug-in terminal block, 10-pin

#### Hardware

Bypass:	N/A
CPU:	NXP i.MX 8M Mini ARMv8 64-bit Cortex-A53 @ 1.6 GHz (quad core)
Encryption:	TPM 2.0 (Trusted Platform Module)
Memory:	LPDDR4 4 GB
Storage:	64 GB eMMC storage

#### Power requirements

Operating Voltage:	Dual 10 ~ 30 V DC
Power consumption:	2.5 - 12W

#### Security features

Multipoint VPN:	External connectivity via OpenVPN, IPsec or Belden Horizon™ console
-----------------	---

#### Service

Protocols:	SNMPv3, HTTPS, SSL-VPN, L2TP, Ping, NTP (Client/ Server), DNS, Dynamic DNS, DHCP (Server/Client), Syslog
------------	--

#### Software

Redundancy:	Routing between LAN and WAN, WAN Backup
Management:	Local Web UI for configuration, diagnostics and maintenance, Supports FTP/SFTP through Belden Horizon™ console
Diagnostics:	LEDs (Power, Link Status, Data, Status), Signal Contact (24 V DC/1 A), Log File, Syslog
Configuration:	Web Interface, Belden Horizon™ Console

Security:	Integrated Firewall , Allowed IP List to prevent unwanted access , Secure Socket Tunneling Protocol (SSTP, port 443) with single use credentials to create tunnels , AES-256 bit encryption , Activity Logs Additional IT-friendly security features when using Belden Horizon™ Console (formerly ProSoft Connect™, a secure, cloud-native platform for the Industrial Internet of Things): , • Virtual Lockout, Tagout (vLOTO™) – dynamic authorization for secure remote access , • Active Directory support via Single Sign On (SSO) with SAML 2.0 , • Email and Token based multi factor authentication , • Role based access for users and devices , • Configure password rules and enforcement policies , • Audit trail with auto-backup
Miscellaneous:	NTP Client and Server, DHCP Client, DNS Client
Routing:	Routing between LAN and WAN, WAN Backup, IP masquerading, 1-to-1 NAT, port forwarding, L2 bridging
Application Support and Management:	Docker Containers, Docker Compose, App orchestration through Belden Horizon™ console, Docker Compose

Ambient conditions

Operating temperature:	-40-+70 °C
Storage/transport temperature:	-40-+85 °C
Relative humidity (non-condensing):	5-95 %

Mechanical construction

Dimensions (WxHxD):	48 x 137 x 105 mm
Weight:	613 g
Housing Material:	Aluminum with DIN clip
Mounting:	DIN Rail 35 mm

Approvals

Basis Standard:	CE, FCC
Safety of information technology equipment:	UL 61010
Hazardous locations:	ISA-12.12.-01 Class 1 Div. 2 – Haz. Loc, ATEX-95 Category 3G (Zone 2)

Reliability

Guarantee:	60 months (please refer to the terms of guarantee for detailed information)
------------	---

Further Instructions

Product Documentation:	<a href="https://www.doc.hirschmann.com/index.html">https://www.doc.hirschmann.com/index.html</a>
Certificates:	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>
Software Download:	<a href="https://hirschmann-support.belden.com/en-US/news/edge">https://hirschmann-support.belden.com/en-US/news/edge</a>

History

Update and Revision:	Revision Number: 0.12 Revision Date: 11-05-2024
----------------------	---

Variants

Item #	Type
942332003	OpEdge-4D

© 2024 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.