



**Product:** [KCONN Front-Loading PP 24 1U](#)

AX106288, KeyConnect Front-Loading Patch Panel 24 Port, 1U, Empty, UTP

## Product Description

KeyConnect Front Access Patch Panel, 24-port, 1U, Empty

## Technical Specifications

### Product Overview

Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden Systems 10GX, 4800, 3600, 2400 and 1200.
------------------------	---

### Physical Characteristics (Overall)

Overall Height:	43.942 mm
Overall Width:	482.600 mm
Overall Depth:	98.196 mm
Number of Ports:	24 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box. Bezels packaged 24 units per bag
Weight:	0.195 kg

### Connectors

#### Materials

Description	Material	Color
Panel	Steel	Black
Bezel	Polycarbonate	Black
Management Bar	Steel	Black

### Construction and Dimensions

Max Capacity:	24 connectors
---------------	---------------

### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

### Mechanical Characteristics

Connector System Compatibility:	KeyConnect
---------------------------------	------------

### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

### Flammability, LSOH, Toxicity Testing

Safety Listing:	ACA, Bi-national Standard Listed
-----------------	----------------------------------

## Related Part Numbers

Related Parts:	Compatible with 10GX, CAT6+, CAT5E Jacks and Couplers, as well as Multimedia KeyConnect Modules
----------------	---

## Variants

Item #	Color	UPC
AX106288	Black	611589182942

## Product Notes

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 24 Bezels; 1 Rear Cable Management Bar; 1 Installation Guide
Notes:	For proper installation refer to Installation Guide PX106172 included with the product or visit our web site at <a href="http://www.belden.com">http://www.belden.com</a>

## History

Update and Revision:	Revision Number: 0.57 Revision Date: 12-03-2025
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.