



Product: [PS-DSCM-OR-B50](#)



DIN Rail Terminal Block Wire Connector Orange 50 PCS

Product Description

DIN Rail Terminal Block Wire Connector Wire dimension 24-12AWG / 0.2-4mm²

Technical Specifications

Physical Characteristics (Overall)

Material:	Contacts 301 stainless steel - Brass (tin-plated) – PA66/PC (Nylon UL94V-2)
Packaging:	50 per package
Weight:	380 g

Electrical Characteristics

Insulation Resistance:	≥1000MΩ
Max Contact Resistance:	15 mOhm
Rated Voltage:	250V/600V

Mechanical Characteristics

Dimensions (WxHxD)

Length	Width	Height
43.0 mm	8.2 mm	30.8 mm

Product Notes

Notes:	* Packaging: Carton Box (220 mm x 90 mm x 40 mm) includes 50 pcs * One package weight is 380 g. * Applicable Bare Conductor Size: 24 - 12 AWG (0.2 - 4 mm ²) * Max Outer Jacket Diameter: ≤ 5.0 mm * Stripping Length: 8 - 10 mm
--------	--

History

Update and Revision:	Revision Number: 0.13 Revision Date: 02-13-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.