



Product: [RA6MJ](#)

DataConnect CAT 6 RJ45 Modular Jack UTP

Product Description

DataConnect CAT 6 RJ45 Modular Jack UTP, KeyConnect style

Technical Specifications

Product Overview

Suitable Applications:	TIA Category 6, ISO Class E, UTP 1000 BASE-T
------------------------	--

Physical Characteristics (Overall)

Packaging:	Individually packaged in a clear plastic bag.
------------	---

Connectors

Materials

Description	Material
Jack House	PC/ABS
RJ45 Contact Material & Finish	Phosphor bronze plated with 30 μ inch gold over nickel undercoat
IDC Housing	PC
Termination Wire Diameter Range	23~26 AWG, Stranded or Solid

Electrical Characteristics

Dielectric Strength:	1000 V, 1min
Insulation Resistance:	500 MOhm
Max Contact Resistance:	20 mOhm
Termination Resistance:	0.2 Ohm

Mechanical Characteristics

Tool Compatibility:	Belden 110 Connecting Tool
Plug /Jack Compatibility:	RJ45
Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	IDC Connection
Termination Rear Connection Durability:	20 cycles
Plug/Connector Retention:	50 N

Standards

Data Category:	Category 6
TIA/EIA Compliance:	TIA/EIA 568-2.D

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Product Notes

Included Parts:	Termination wire cover
-----------------	------------------------

History

Update and Revision:	Revision Number: 0.8 Revision Date: 06-24-2022
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.