

Product: RAVEN 4300M-4T4F

Power supply via IDS



RAVEN Media Module for RAVEN 4000 series Intrusion Detection System - RAVEN 4300M-4T4F

Product Description

Media module for RAVEN 4300 IDS

Technical Specifications

Product description

Туре:	RAVEN 4300M-4T4F
Name:	RAVEN 4300M-4T4F
Description:	Media module for RAVEN 4300 IDS
Part Number:	942999720
Port type and quantity:	4 × FE/GE TX ports, 4 × 100/1000M SFP slots

Power requirements

0	perating	Voltage:

Ambient conditions

Permissible Humidity (Storage/Transport):	5% to 95%
Operating temperature:	0-+40 °C
Storage/transport temperature:	-20°C to +70 °C
Relative humidity (non-condensing):	5-85 %

Mechanical construction

Width:	78.4 mm
Height:	39.8 mm
Depth:	195.7 mm
Weight:	0.6 kg

Mechanical stability

IEC 60068-2-6 vibration:	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
IEC 60068-2-27 shock:	15 g, 11 ms duration, 18 shocks

EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD):	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field:	10V/m (80-1000MHz), 3V/m (1000-6000MHz)
EN 61000-4-4 fast transients (burst):	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage:	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
EN 61000-4-6 Conducted Immunity:	10 V (150 kHz-80 MHz)
EN 61000-4-8 power freq magnetic field:	30A/m
EN 61000-4-11 voltagedips, short interrupt:	0%(20ms), 40%(300ms), 70%(500ms), 0%(5s)

EMC emitted immunity

EN 55032:	EN 55032 Class A
EN 61000-3-2:	EN 61000-3-2 Class A

EN 61000-3-3:	EN 61000-3-3
FCC CFR47 Part 15:	FCC 47CFR Part 15, Class A

Approvals

FCC:	Compliant
China Network Access Certificate:	Compliant
RoHS Compliant:	RoHS((EU) 2015/863) and RoHS(GB/T26572-2011) compliant

Scope of delivery and accessories

Accessories to Order Separately:	SFP
Scope of delivery:	Media module
History	
Update and Revision:	Revision Number: 0.10 Revision Date: 05-14-2024

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.