



**Product:** [M13330](#) 

AUDIO, 30C #22, Str, PVC, Semi Rigid, 300 V, AWM/STYLE 2576 80C, CM 75C, CSA C(UL) TYPE CM

## Product Description

AUDIO, 30 Conductor 22 AWG (7/30) TC - Tinned Copper, PVC, Semi Rigid Insulation, Slate PVC Outer Jacket, AWM/STYLE 2576 80C, CM 75C, CSA C(UL) TYPE CM C(UL) TYPE CM

## Technical Specifications

### Product Overview

|                        |                                                                                                                                                                                |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Suitable Applications: | Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems. |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Construction Details

#### Conductor

| Element      | No. of Elements | Size   | Stranding | Material           |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 30              | 22 AWG | 7x30      | TC - Tinned Copper |

#### Insulation

| Element      | Material                                 | Nom. Thickness     | Nom. Insulation Diameter | Color Code                                                                                                                                                                                                                                                                                                                                                                                 |
|--------------|------------------------------------------|--------------------|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor(s) | SR-PVC - Polyvinyl Chloride (Semi-Rigid) | 0.010 in (0.25 mm) | 0.050 in (1.3 mm)        | Black, White, Red, Green, Orange, Blue, White/Black, Red/Black, Green/Black, Orange/Black, Blue/Black, Black/White, Red/White, Green/White, Blue/White, Black/Red, White/Red, Orange/Red, Blue/Red, Red/Green, Orange/Green, Black/White/Red, White/Black/Red, Red/Black/White, Green/Black/White, Orange/Black/White, Blue/Black/White, Black/Red/Green, White/Red/Green, Red/Black/Green |

#### Outer Jacket

| Material                 | Nom. Thickness    | Nom. Diameter      |
|--------------------------|-------------------|--------------------|
| PVC - Polyvinyl Chloride | 0.040 in (1.0 mm) | 0.401 in (10.2 mm) |

|                                   |                    |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.401 in (10.2 mm) |
|-----------------------------------|--------------------|

### Electrical Characteristics

#### Electricals

| Element      | Nom. Capacitance Cond-to-Cond | Nom. Inductance        |
|--------------|-------------------------------|------------------------|
| Conductor(s) | 22.8 pF/ft (74.8 pF/m)        | 0.18 µH/ft (0.59 µH/m) |

#### Voltage

| UL Voltage Rating            |
|------------------------------|
| 300 V (CM), 150 V (AWM 2576) |

### Mechanical Characteristics

#### Temperature

| UL Temperature | Operating      |
|----------------|----------------|
| 80°C           | -20°C To +80°C |

#### Bend Radius

| Stationary Min. |
|-----------------|
| 4.0 in (100 mm) |

|                    |                  |
|--------------------|------------------|
| Max. Pull Tension: | 246 lbs (112 kg) |
|--------------------|------------------|

Standards and Compliance

|                                |                                                                                                                      |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------|
| Environmental Suitability:     | Indoor                                                                                                               |
| Sustainability:                | CA Prop 65                                                                                                           |
| NEC / UL Compliance:           | Article 800, CM                                                                                                      |
| AWM Compliance:                | AWM 2576                                                                                                             |
| CEC / C(UL) Compliance:        | CM                                                                                                                   |
| European Directive Compliance: | EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance:      | UKCA Mark                                                                                                            |
| APAC Compliance:               | China RoHS II (GB/T 26572-2011)                                                                                      |

Product Notes

|        |                                                                                         |
|--------|-----------------------------------------------------------------------------------------|
| Notes: | Alpha Wire -* P/N M13330 30C 22 AWG EXXXXXX 75C CM (UL) C(UL) OR AWM STYLE 2576 CE ROHS |
|--------|-----------------------------------------------------------------------------------------|

History

|                      |                                                 |
|----------------------|-------------------------------------------------|
| Update and Revision: | Revision Number: 0.28 Revision Date: 08-29-2026 |
|----------------------|-------------------------------------------------|

Part Numbers

Variants

| Item #       | Color | Putup Type | Length |
|--------------|-------|------------|--------|
| M13330 SL005 | Slate | Reel       | 100 ft |

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.