



Product: [RK 190M-769](#)



1-1/8" Molded Female Cordset, Contacts: 19, 300 V | 3 A & 8 A , IP67; Cable TPE Yellow, 19x18AWG; cURus 2238

Product Description

1-1/8" Molded Female Cordset, Contacts: 19, 300 V | 3 A & 8 A , IP67; Cable TPE Yellow, 19x18AWG; cURus 2238

Technical Drawing

Female Face View	Contact	Conductor Color	Current
	1	BK# 1	3 A
	2	BK# 2	
	3	BK# 3	
	4	BK# 4	6 A
	5	BK# 5	
	6	BK# 6	3 A
	7	BK# 7	3 A
	8	BK# 8	3 A
	9	BK# 9	
	10	BK# 10	
	11	BK# 11	⊕
	12	GN YE	
	13	BK# 13	3 A
	14	BK# 14	
	15	BK# 15	
	16	BK# 16	
	17	BK# 17	
	18	BK# 18	
	19	BK# 19	



Technical Specifications

Technical Data

Product Family:	Power Connector
Product Sub Family:	1-1/8" RK Female
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	Female
Connector Design:	Straight
Number of Pins:	19
Coding:	A
Shielding:	Unshielded
Attachment Type:	Coupling nut with internal threads
Rated Voltage:	300 V
Mating Cycles:	≤ 50
Ambient Temperature (Operation)*:	-40 °C to +90 °C
Protection Degree / IP Rating**:	IP65, IP67

Materials

Contact Base Material:	CuZn
Contact Plating:	Au over Ag
Contact Bearer Material:	TPU
Contact Bearer Color:	YE
Molded Body Material:	TPU
Molded Body Color:	yellow

Attachment Material:	Anodized Bk, Al
----------------------	-----------------

Additional Technical Data

Accessories to Order Separately:	500000358 - RS-TU thread adaptor
----------------------------------	----------------------------------

Cable Data

Cable Number:	769
Conductor Size:	18 AWG
Number of Wires:	19
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 5 Mio.
Cable Jacket Material:	TPE
Cable Jacket Color:	Yellow
Cable Diameter D:	Ø 13.46 mm
Wire Insulation Material:	PVC-Nylon
Insulated Wire Diameter:	Ø 2.00 mm
Ambient Temperature (Fixed Installation):	-40 C° - +90 C°
UL Cable Type:	(UL) PLTC or AWM 20626
Flammability Class (Cable Jacket):	I/II A/B, CSA FT4
Cable Characteristics:	Oil and Coolant, Vibration, UV, Abrasion, and Weld Spark resistant, Continuous Flex

Approvals

UL-File:	Do not connect or disconnect under load.
UL:	UL 2238; cURus

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Note Derating:	Notice Derating
----------------	-----------------

History

Update and Revision:	Revision Number: 0.36 Revision Date: 04-10-2025
----------------------	---

Variants

Item #	Item Description	Cable Length
500004042	RK 190M-769/2M	2 m
500003259	RK 190M-769/5M	5 m
540001299	RK 190M-769/6M	6 m
500003260	RK 190M-769/10M	10 m
500004041	RK 190M-769/15M	15 m
500003261	RK 190M-769/20M	20 m
540000818	RK 190M-769/25M	25 m
540000778	RK 190M-769/30M	30 m
540002246	RK 190M-769/40M	40 m
540003182	RK 190M-769/50M	50 m
540003183	RK 190M-769/60M	60 m

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.