



**Product:** [MA6UFL](#) 

MarineTuff Cat 6, U/FTP, 4 Pr 23 BC, FMPE Ins, LSZH, Indoor, LR certified

## Product Description

Marine Ethernet Cat 6, 4 Pr 23AWG Annealed Bare Copper, Foam Polyethylene Insulation, U/FTP, Low Smoke Zero Halogen (SHF1) Jacket, Indoor Shipboard, LR certified

## Technical Specifications

### Product Overview

Suitable Applications:	Shipbuilding, in-cabin passenger Wi-Fi, high-bandwidth IPTV, PoE lighting, device charging stations, onboard security cameras, etc.
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

#### Insulation

Material	Nominal Diameter
PO - Polyolefin (Foam)	1.35 mm

#### Color Chart

Number	Color
Pair 1	White & Blue
Pair 2	White & Orange
Pair 3	White & Green
Pair 4	White & Brown

#### Inner Shield

Type	Material
Tape	Bi-Laminate (Alum+Poly)

#### Outer Shield

Drainwire Material	Drainwire AWG
Tinned Copper	28 AWG

#### Outer Jacket

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (SHF1)	7.5 mm	0.3 mm

### Construction and Dimensions

Min Elongation at Break of Jacket:	125 %
Min Tensile Strength of Jacket:	9 MPa
Min Tensile Strength of Jacket Aged:	30 %
Min Elongation at Break of Jacket Aged:	30 %

## Electrical Characteristics

### Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]	Max. DCR Unbalanced Within Pair [%]
95 Ohm/km	4 %	2 %

### Capacitance

Max. Capacitance Unbalance	Max. Mutual Capacitance
160 pF/100m	56 pF/m

Insulation Resistance:	5000 MOhm.m
------------------------	-------------

### Impedance

Nominal Characteristic Impedance
100 Ohm

### Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
45 ns/100m	77%

### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	75.3 dB	72.3 dB	73.2 dB	70.2 dB	68 dB	65 dB	20 dB	40 dB	35 dB
4 MHz	3.8 dB/100m	66.3 dB	63.3 dB	62.4 dB	59.4 dB	56 dB	53 dB	23 dB	34 dB	23 dB
10 MHz	6 dB/100m	60.3 dB	57.3 dB	54.3 dB	51.3 dB	48 dB	45 dB	25 dB	30 dB	15 dB
16 MHz	7.6 dB/100m	57.2 dB	54.2 dB	49.6 dB	46.6 dB	43.9 dB	40.9 dB	25 dB	28 dB	10.9 dB
31.3 MHz	10.7 dB/100m	52.9 dB	49.9 dB	42.1 dB	39.1 dB	38.1 dB	35.1 dB	23.6 dB	25.1 dB	5.1 dB
62.5 MHz	15.5 dB/100m	48.4 dB	45.4 dB	32.9 dB	29.9 dB	32.1 dB	29.1 dB	21.5 dB	22 dB	
100 MHz	19.9 dB/100m	45.3 dB	42.3 dB	25.4 dB	22.4 dB	28 dB	25 dB	20.1 dB	20 dB	
125 MHz	22.5 dB/100m	43.8 dB	40.8 dB	21.4 dB	18.4 dB	26.1 dB	23.1 dB	19.4 dB	19 dB	
200 MHz	29.1 dB/100m	40.8 dB	37.8 dB	11.6 dB	8.6 dB	22 dB	19 dB	18 dB	17 dB	
250 MHz	33 dB/100m	39.3 dB	36.3 dB	6.3 dB	3.3 dB	20 dB	17 dB	17.3 dB	16 dB	

Table Notes:	Limits below 4 MHz are for information only. Reference standard: ISO/IEC 61156-5 ed. 2.0 (2009)
Coupling Attenuation Class:	Type Ib
Transfer Impedance Class:	Grade 2

### Voltage

Voltage Rating [V]
72 V DC

## Temperature Range

Installation Temperature Range:	-5°C To +80°C
Operating Temperature Range:	-40°C To +80°C

## Mechanical Characteristics

Bending Test:	Low temperature bending test -40 °C : No cracks
Pressure Test for Jacket:	Test at high temperature IEC 60811-508 80±2 °C 4h : ≤ 50 %
Heat Stroke Test:	Heat Shock test at (150±3°C , 1h) : No cracks
Bulk Cable Weight:	57.3 kg/km
Min. Bend Radius During Installation:	10*D

## Standards

ISO/IEC Compliance:	ISO/IEC 11801-2, IEC 60092-360
CENELEC Compliance:	EN 50173-1
Data Category:	Category 6
ANSI Compliance:	ANSI/TIA 568.2-D (2018)
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4

## Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2, IEC 60332-3-22
Fluorine Content Test IEC60684-2:	HF ≤ 0.1%
IEC 60754-1 - Halogen Amount:	HCL+HBr ≤ 0.5%
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	10 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

## Related Part Numbers

Footnote:	*Ordering stock code will be created at the time of placing the order and the stock code will include cable part code, outer jacket color & putup length.
-----------	---

## Product Notes

Notes:	LR (Lloyd's Register) certification
--------	-------------------------------------

## History

Update and Revision:	Revision Number: 0.48 Revision Date: 11-09-2022
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.