



Product: [MA7SFL](#)

MarineTuff Cat 7, S/FTP, 4 Pr 23 BC, FMPE Ins, LSZH, Indoor, LR certified

Product Description

Marine Ethernet Cat 7, 4 Pr 23AWG Annealed Bare Copper, Foam Polyethylene Insulation, S/FTP, Low Smoke Zero Halogen (SHF1) Jacket, Indoor Shipboard, LR certified

Technical Specifications

Product Overview

Suitable Applications:	Shipbuilding, in-cabin passenger Wi-Fi, high-bandwidth IPTV, PoE lighting, device charging stations, onboard security cameras, etc.
------------------------	---

Construction Details

Conductor

Stranding	Material	No. of Pairs
Solid	BC - Bare Copper	4

Insulation

Material	Nom. Insulation Diameter	Color Code
PO - Polyolefin (Foam)	1.35 mm (0.0531 in)	White & Blue, White & Orange, White & Green, White & Brown

Inner Shield

Element	Shield Type	Material	Coverage
Individual Shielded Pair	Tape	Bi-Laminate (Alum+Poly)	100%

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	30%

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (SHF1)	7.8 mm (0.31 in)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
95 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
25 ns/100m	78%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2.1	78	75	75.9	72.9	78	75	20	40	35
4	3.7	78	75	74.3	71.3	78	75	23	34	23
10	5.8	78	75	72.2	69.2	74	71	25	30	15
16	7.3	78	75	70.7	67.7	69.9	66.9	25	28	10.9

31.3	10.3	78	75	67.7	64.7	64.1	61.1	23.6	25.1	5.1
62.5	14.6	75.5	72.5	60.9	57.9	58.1	55.1	21.5	22	
100	18.5	72.4	69.4	53.9	50.9	54	51	20.1	20	
125	20.8	70.9	67.9	50.2	47.2	52.1	49.1	19.4	19	
200	26.5	67.9	64.9	41.4	38.4	48	45	18	17	
250	29.7	66.4	63.4	36.7	33.7	46	43	17.3	16	
300	32.7	65.2	62.2	32.6	29.6	44.5	41.5	17.3		
500	42.8	61.9	58.9	19.2	16.2	40	37	17.3		
600	47.1	60.7	57.7	13.6	10.6	38.4	35.4	17.3		

Table Notes:	Limits below 4 MHz are for information only. Reference standard: ISO/IEC 61156-5 ed. 2.0 (2009)
Transfer Impedance Class:	Grade 2

Mechanical Characteristics

Temperature

Operating	Installation
-40°C To +80°C	-5°C To +80°C

Bend Radius

Installation Min.
10"D

Bulk Cable Weight:	65.5 kg/km (44.0 lbs/1000ft)
--------------------	------------------------------

Standards and Compliance

Environmental Suitability:	Indoor, Indoor
Flammability / Reaction to Fire:	UL1581 VVW-1, IEC 60332-1-2, IEC 60332-3-22
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 7
ISO/IEC Compliance:	ISO/IEC 11801-2IEC 60092-360
CENELEC Compliance:	EN 50173-1
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = HCL+HBr ≤ 0.5%, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 μS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3

Product Notes

Notes:	LR (Lloyd's Register) certification
--------	-------------------------------------

History

Update and Revision:	Revision Number: 0.67 Revision Date: 04-29-2024
----------------------	---

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.