



Product: [MDBU54AA024EVAA](#) 

Indoor Mini-distribution 24 Fibers OM4

Product Description

Indoor Mini-distribution fiber cable, OM4, 24F, LSZH Jacket, IEC 60332-3-24

Technical Specifications

Product Overview

Construction Type:	Mini Distribution
Environmental Space:	Indoor
Suitable Applications:	High degree of flexibility suitable for horizontal, interconnect applications; Excellent LSZH flame retardant performance for indoor application

Material

Fiber Cable Construction

Fiber Type	Fiber Count	Subunit Color
OM4	24	Erika Violet

Fiber Color Code:	TIA coding (Gxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua
Central Strength Member Type:	GRP
Bulk Cable Weight:	36 kg/km

SubUnit Specifications

Number of Active Subunits:	2
Subunit Diameter:	2.0 mm

Physical Specifications

Number Of Fillers @Stranding1:	2
--------------------------------	---

Jacket Specifications

Number of Jackets:	Single Jacket
Type of Armor:	Non-Armored

Outer Jacket Specifications

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.5 mm	0.65 mm

Optical Characteristics

Fiber Core Diameter:	50 ±2.5 µm
Maximum Attenuation at 1300 nm:	1.0 dB/km
Maximum Attenuation at 850 nm:	3.0 dB/km

Mechanical Characteristics

Mechanical Tests

Description	Tested Standard	Requirement/Value
-------------	-----------------	-------------------

Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E11	20 x Cable OD
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	10 x Cable OD
Cable Max. Tensile Strength Installation (Short Term)	IEC 60794-1-21-E1	660 N (148 lbf)
Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	200 N (45 lbf)
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3	1000 N/100mm

Temperature Range

Operating Temperature Range:	-20 °C to +60 °C
Storage Temperature Range:	-20 °C to +60 °C

Standards

UL Rating/Flame Test:	Non-UL Rated
IEC Flammability:	IEC 60332-3-24
TIA/EIA Compliance:	EIA/TIA-455
ISO/IEC Compliance:	IEC 60793-1-1, IEC 60794-1-1
EU Directive 2011/65/EU (RoHS 2):	Compliant

History

Update and Revision:	Revision Number: 0.23 Revision Date: 12-07-2023
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.