



Product: [MDVO LC Keyed Dup MM Adapters](#)

MDVO LC Keyed Duplex Multimode Adapter



Product Description

MDVO LC Keyed Duplex Multimode Adapter. Available in several colors.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Secured applications over fiber optic

Construction

Weight:	0.01 kg
Height:	0.63 m
Width:	0.63
Depth:	1.14

Mechanical Characteristics

Footprint/Type:	MDVO
-----------------	------

Temperature Range

Operating Temperature Range:	-10 to 60°C
Storage Temperature Range:	-40 to 70°C

Product Material

Materials

Description	Material	Type
Front Connection	Plastic - UL94V-0	LC Keyed
Rear Connection	Plastic - UL94V-0	LC Keyed
Insert	Plastic - UL94V-0	MDVO

Standards

Safety Listing:	Bi-national Standard Listed
-----------------	-----------------------------

Related Part Numbers

Related Parts:	Compatible MDVO Faceplate and Patch Panel
----------------	---

Variants

Item #	Color	Port Count	Adapter Color
AX102095	Almond	1 Port	Red
AX102096	Almond	1 Port	Green
AX102097	Almond	1 Port	Yellow
AX102098	Almond	1 Port	Black
AX102099	Almond	1 Port	Orange
AX102100	Almond	1 Port	Blue
AX102104	Black	1 Port	Black

AX102107	Black	1 Port	Red
AX102108	Black	1 Port	Green
AX102109	Black	1 Port	Yellow
AX102110	Black	1 Port	Black
AX102111	Black	1 Port	Orange
AX102112	Black	1 Port	Blue
AX102089	Gray	1 Port	Red
AX102090	Gray	1 Port	Green
AX102091	Gray	1 Port	Yellow
AX102092	Gray	1 Port	Black
AX102093	Gray	1 Port	Orange
AX102094	Gray	1 Port	Blue
AX102101	Red	1 Port	Red
AX102102	White	1 Port	Green
AX102103	White	1 Port	Yellow
AX102105	White	1 Port	Orange
AX102106	White	1 Port	Blue

Product Notes

Packaging:	10 Modules packaged in a suitable plastic bag.
------------	--

History

Update and Revision:	Revision Number: 0.62 Revision Date: 11-09-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.