



**Product:** [MDVO SC MODULE](#)

MDVO SC Fiber Module

## Product Description

MDVO SC Fiber Module. Available in several colors and fiber types.

## Technical Specifications

### Product Overview

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room
------------------------	---

### Physical Characteristics (Overall)

Height:	0.63 m
Width:	0.63
Depth:	1.31
Front Connection:	Flush
Packaging:	10 units packaged in a plastic bag.
Weight:	0.013 lbs

### Connectors

#### Materials

Description	Material	Type
Front Connection	Plastic - UL94V-0	SC-Simplex
Rear Connection	Plastic - UL94V-0	SC-Simplex

### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

### Mechanical Characteristics

Footprint/Type:	MDVO
Connector/Hardware Retention:	20 lbs

### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

### Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

### Related Part Numbers

Related Parts:	Compatible MDVO-style Faceplate and Patch Panel, SC Fiber Patch Cord
----------------	--

#### Variants

Item #	Color	UPC
A0407004	Almond	611589000529
AX104624-02	Almond	611589077583
AX105697-AL	Almond	611589158466
AX105698-AL	Almond	611589158497
A0407006	Black	611589000543
AX104624-04	Black	611589077606
AX105697-BK	Black	611589158473
AX105698-BK	Black	611589158503
A0407003	Gray	611589000512
AX104624-01	Gray	611589077576
AX105697-GY	Gray	611589158459
AX105698-GY	Gray	611589158510
AX102596	Ivory	611589027670
AX104624-12	Ivory	611589077613
A0407005	White	611589000536
AX104624-03	White	611589077590
AX105697-WH	White	611589158480
AX105698-WH	White	611589158527

## Product Notes

Included Parts:	Dust Caps
Notes:	For additional information about this product, visit our web site at <a href="http://www.belden.com">http://www.belden.com</a>

## History

Update and Revision:	Revision Number: 0.181 Revision Date: 03-04-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.