

**Part Number: MEDIAFLEX DG FACEPLATES**



MediaFlex 2-Gang Faceplates

**Product Description**

MediaFlex Faceplate, Double Gang

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, Fiber and Coax.

**Physical Characteristics (Overall)**

Height:	4.5 m
Width:	5.18
Depth:	0.77
Front Connection:	Flush
Packaging:	Individually packaged in a plastic bag.

**Connectors**

**Materials**

Description	Material
Faceplate	Plastic - UL94V-0

**Temperature Range**

Installation Temp Range:	-10 to 60°C
Storage Temp Range:	-40 to 70°C
Operating Temp Range:	-10 to 60°C

**Mechanical Characteristics**

Footprint/Type:	Mediaflex
-----------------	-----------

**Applicable Environmental and Other Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-07
MII Order #39 (China RoHS):	EUP 50

**Flammability, LS0H, Toxicity Testing**

Safety Listing:	ACA, Bi-national Standard Listed
-----------------	----------------------------------

**Part Number**

Related Parts:	Compatible with MediaFlex Inserts
----------------	-----------------------------------

**Variants**

Item #	Color
AX101870	Almond
AX101872	Black

AX101871	Electric White
AX101869	Gray
AX102570	Ivory
AX102609	White

## Product Notes

Included Parts:	Windows, paper, 6-32 screws, installation guide
Notes:	For proper installation refer to Installation Guide PX102063 included with the product or visit our web site at <a href="http://www.belden.com">http://www.belden.com</a>

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.