



**Product:** [MEDIAFLEX ANGLED EDGE SG PLATE](#)

## MediaFlex Angled Edge 1-Gang Faceplate

### Product Description

MediaFlex Angled Edge Faceplate, Single Gang. Available in several colors.

### Technical Specifications

#### Product Overview

Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800,3600, 2400 and 1200
------------------------	--

#### Physical Characteristics (Overall)

Height:	4.5 m
Width:	2.75
Depth:	0.455
Front Connection:	Angled
Packaging:	Individually packaged in a plastic bag.
Weight:	0.069 kg

#### Connectors

##### Materials

Description	Material
Faceplate	High-impact Thermoplastic, flame-retardant UL94V-0, UV-resistant

#### Temperature Range

Installation Temperature Range:	-10 to 60°C
Storage Temperature Range:	-40 to 70°C
Operating Temperature Range:	-10 to 60°C

#### Mechanical Characteristics

Footprint/Type:	Mediaflex
-----------------	-----------

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

#### Related Part Numbers

Related Parts:	Compatible with MediaFlex Modules
----------------	-----------------------------------

##### Variants

Item #	Color
AX106670	Almond
AX106672	Black
AX106671	Electric White
AX106669	Gray

## Product Notes

Included Parts:	windows, papers, 6-32 screws, installation guide
Notes:	For proper installation refer to Installation Guide PX106224 included with the product or visit our web site at <a href="http://www.belden.com">http://www.belden.com</a>

## History

Update and Revision:	Revision Number: 0.61 Revision Date: 03-04-2023
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.