



**Product:** [MSHCY030](#)

MachFlex™ SERVO Hybrid 610BCY, 3C+1G 10mm² Str BC, PP Ins, 1 Pr 1.0mm² BC, PP Ins IS, Overall TC Brd, PVC Jkt

### Product Description

MachFlex™ SERVO Hybrid 610BCY, 3 Conductor +1 Ground 10mm² Stranded Bare Copper, PP Insulation, 1 Pair 1.0mm² Bare Copper, PP Insulation, Aluminium Foil Plus Tinned Copper Braid Shield Over Each pair, Overall Tinned Copper Braid Shield, PVC Outer Jacket, 1000V Flexible SERVO Motor Supply Cable

### Technical Specifications

#### Product Overview

**Suitable Applications:** Designed for connecting servo controller with motor. Cable applications include motor speed control, printing machine, production machinery and machine tools. This type of cables suitable for plant engineering both of static or flexible use. Signal pair shield plus overall shield ensure good performance on EMI/RFI resistance.

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Stranding Class	Material
Conductor(s)	3	10 mm²	Stranded	Class 5	BC - Bare Copper
Ground	1	10 mm²	Stranded	Class 5	BC - Bare Copper
Signal Pair(s)	1	1 mm²	Stranded	Class 5	BC - Bare Copper

##### Insulation

Element	Material	Color Code
Conductor(s)	PP - Polypropylene	Black #1, Black #2, Black #3
Ground Wire	PP - Polypropylene	Yellow/Green
Pair(s)	PP - Polypropylene	White&Brown

##### Inner Shield

Element	Shield Type	Material	Coverage
Each Pair	Tape	Bi-Laminate (Alum+Poly)	100%
Each Pair	Braid	Tinned Copper (TC)	85%

##### Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	85%

##### Outer Jacket

Material
PVC - Polyvinyl Chloride

Overall Cable Diameter (Nominal): 18.7 mm (0.736 in)

#### Electrical Characteristics

##### Voltage

UL Voltage Rating	Voltage Rating
1000 V (Max. Operating Voltage)	600/1000 V (Max. Operating Voltage), 4000 V (Testing Voltage)

#### Mechanical Characteristics

## Temperature

Operating	Installation
-5°C to +80 °C (Occasional movement)	-40°C to +80°C (Fixed installation)

## Bend Radius

Installation Min.	Flexing Min.
112.2 mm (4.417 in)	280.5 mm (11.04 in)

Bulk Cable Weight: 651 kg/km (437 lbs/1000ft)

## Standards and Compliance

Environmental Suitability:	Sunlight Resistance, UV Resistance, Oil Resistance - 70°C x 4h
Flammability / Reaction to Fire:	VW-1, FT1, IEC 60332-1-2, DIN VDE 0482-332-1-2, DIN EN 60332-1-2
AWM Compliance:	AWM 2570
CENELEC Compliance:	EN 50290-2-25EN 50363-4-1
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2)

## History

Update and Revision: Revision Number: 0.111 Revision Date: 07-05-2024

## Part Numbers

### Variants

Item #	Color	Length
MSHCY030 003100M	Orange, RAL 2003	100 m
MSHCY030 003200M	Orange, RAL 2003	200 m
MSHCY030 003300M	Orange, RAL 2003	300 m

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.